

Product: [MTM8000-16Q-A](#) 

MAMMUTHUS Media Module for MTS8000 Series Switch



Product Description

Media module for MTS8000 series modular switch, layer 3 forwarding card

Technical Specifications

Product description

| | |
|-------------------------|---|
| Type: | MTM8000-16Q-A |
| Description: | Media module for MTS8000 series modular switch, layer 3 forwarding card |
| Part Number: | 942999812 |
| Port type and quantity: | 16 × 40G QSFP+ slots |

Power requirements

| | |
|--------------------|-------------------------|
| Operating Voltage: | Power supply via switch |
| Power consumption: | 230W |

Ambient conditions

| | |
|---|------------|
| Permissible Humidity (Storage/Transport): | 5% to 95% |
| Operating temperature: | 0-+55 °C |
| Storage/transport temperature: | -40-+70 °C |
| Relative humidity (non-condensing): | 10-90 % |

Mechanical construction

| | |
|---------|---------|
| Width: | 437 mm |
| Height: | 46 mm |
| Depth: | 402 mm |
| Weight: | 4.78 kg |

Mechanical stability

| | |
|--------------------------|---|
| IEC 60068-2-6 vibration: | 1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min |
| IEC 60068-2-27 shock: | 15 g, 11 ms duration, 18 shocks |

EMC interference immunity

| | |
|--|---|
| EN 61000-4-2 electrostatic discharge (ESD): | 4 kV contact discharge, 8 kV air discharge |
| EN 61000-4-3 electromagnetic field: | 10V/m (80-1000MHz), 3V/m (1000-6000MHz) |
| EN 61000-4-4 fast transients (burst): | 2 kV power line, 1 kV data line |
| EN 61000-4-5 surge voltage: | power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line |
| EN 61000-4-6 Conducted Immunity: | 10 V (150 kHz-80 MHz) |
| EN 61000-4-8 power freq magnetic field: | 30A/m |
| EN 61000-4-11 voltage dips, short interrupt: | 0%(20ms), 40%(300ms), 70%(500ms), 0%(5s) |

EMC emitted immunity

| | |
|---------------|----------------------|
| EN 55032: | EN 55032 Class A |
| EN 61000-3-2: | EN 61000-3-2 Class A |
| EN 61000-3-3: | EN 61000-3-3 |

| | |
|--------------------|----------------------------|
| FCC CFR47 Part 15: | FCC 47CFR Part 15, Class A |
|--------------------|----------------------------|

Approvals

| | |
|-----------------------------------|--|
| FCC: | CE/FCC Compliant |
| China Network Access Certificate: | Compliant |
| Common Criteria: | EAL 2+ |
| RoHS Compliant: | RoHS ((EU) 2015/863) and RoHS (GB/T26572-2011) compliant |

Scope of delivery and accessories

| | |
|----------------------------------|--------------|
| Accessories to Order Separately: | SFP |
| Scope of delivery: | Media module |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.63 Revision Date: 05-23-2024 |
|----------------------|---|

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.