



Product: [NH50107SF](#)

BELDEN CAT7 Ethernet Fire Resistance Rail Cable RoHS

Product Description

BELDEN CAT7 Ethernet IEC 60331-23 EN50200 EN 50289-4-16 Fire Resistance EN 45545-2 TJ-CL313 RAIL Cable RoHS

Technical Specifications

Product Overview

Suitable Applications:	For railway Ethernet Networking, Fire resistance
------------------------	--

Construction Details

Conductor

Size	Material
23 AWG	TC - Tinned Copper

Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
PO - Polyolefin (Foam)	1.4 mm (0.055 in)	Blue, White, Orange, Green, Brown	Fire resistance tape wrapped over insulated cores

Inner Shield

Shield Type	Material
Tapes (Each Pair)	Bi-Laminate (Alum+Poly)

Outer Shield

Shield Type	Material	Coverage
Tape	Polyester + Bi-Laminate (Alum+Poly)	
Braid	Tinned Copper (TC)	80%

Outer Jacket

Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)

Table Notes:	E-beam cross-linked LSZH
Overall Cable Diameter (Nominal):	10.5 mm (0.413 in)

Electrical Characteristics

Electricals

Max. Conductor DCR
71.9 Ω /km

Table Notes:	Nom. fitted Impedance (Ω) 100
--------------	--

High Frequency

Frequency	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]
4	5.6 dB/100 m	78	75	78	77.1	23
10 MHz	8.8 dB/100 m	78	75	71.1	68.1	25
20 MHz	12.4 dB/100 m	78	75	63.8	60.8	25
25 MHz	13.9 dB/100 m	78	75	61.4	58.4	25

31.25 MHz	15.6 dB/100 m	78	75	58.9	55.9	23.3
62.5 MHz	22.3 dB/100 m	75.5	72.5	50.6	47.6	20.7
100 MHz	28.5 dB/100 m	72.4	69.4	44.5	41.5	19
250 MHz	46.5 dB/100 m	66.4	63.4	30.6	27.6	15.6
300 MHz	51.3 dB/100 m	65.2	62.2	27.4	24.4	15.6
600 MHz	75.1 dB/100 m	60.7	57.7	13.4	10.4	15.6

Voltage

UL Voltage Rating	Breakdown Voltage
300 V	2kV ac/min

Mechanical Characteristics

Temperature

Operating
-40 to + 80

Bulk Cable Weight:	112 kg/km (75.3 lbs/1000ft)
--------------------	-----------------------------

Standards and Compliance

Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-25, IEC 60331-23, BS EN 50200 PH120
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 70%
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = 0.5%, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 , IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	BS EN 50289-4-16, T/J/CL 313

Product Notes

Notes:	IEC 61156-6, UL 758 ; Toxicity of insulation (EN 45545-2 Table 5-R15 and R16-HL3) 6 ; Toxicity of jacket (EN 45545-2 Table 5-R15 and R16-HL3) 6 ; Hazard level (EN 45545-2) HL3
--------	---

History

Update and Revision:	Revision Number: 0.4 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.