



Product: [NN01302](#)

DataTwist 2400 Category 6+ Cable, 2 x 4 Pair, U/UTP, LSZH Indoor CPR Dca

Product Description

Category 6 Enhanced Premise Horizontal Cable (300MHz) shotgun, 2 x 4-Pair, 24 AWG Solid Bare Copper Conductors, U/UTP, Polyethylene Insulation, LSZH Jacket

Technical Specifications

Product Overview

Suitable Applications:	Horizontal and building backbone cable; Support current and future Category 6 and 5e applications, such as: 1000Base - T (Gigabit Ethernet), 100 Base - T, 10 Base - T, FDDI, ATM
------------------------	---

Construction Details

Conductor

Element	Size	Stranding	Material	No. of Pairs	No. of Elements
Individual Pair	24 AWG	Solid	BC - Bare Copper	8	16

Insulation

Element	Material	Nom. Insulation Diameter	Color Code
Individual Pair	PE - Polyethylene	1 mm (0.039 in)	White/Blue & Blue, White/Orange & Orange, White/Green & Green, White/Brown & Brown

Cable Core

Description
4 pairs twisted together

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	5.5 mm (0.22 in)

Table Notes:	Figure 8 construction
Overall Cable Diameter (Nominal):	5.5 mm (0.22 in)

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
94 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
45 ns/100m	60%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1	2 dB/100m	75.3	73.3	73.3	71.3	70.8	67.8	20	40	35
4	3.7 dB/100m	66.3	64.3	62.6	60.6	58.8	55.8	23	40	23
10	5.8 dB/100m	61.8	59.8	56	54	50.8	47.8	25	40	15
16	7.4 dB/100m	58.6	56.6	51.2	49.2	46.7	43.7	25	38	10.9
31.2	10.4 dB/100m	54	52	43.6	41.6	40.9	37.9	23.6	35.1	5.1

62.5	15 dB/100m	49.1	47.1	34.1	32.1	34.9	31.9	21.5	32
100	19.3 dB/100m	45.8	43.8	26.5	24.5	30.8	27.8	20.8	30
155	24.5 dB/100m	42.7	40.7	18.2	16.2	27	24	19.5	29
200	28.3 dB/100m	40.9	38.9	12.6	10.6	24.8	21.8	18.7	27
250	32.1 dB/100m	39.3	37.3	7.2	5.2	22.8	19.8	18	26
300	35.6 dB/100m	38.1	36.1	2.5		21.3	18.3	17.5	
350	38.9 dB/100m	37.1	35.1			19.9	16.9	17	
450	45 dB/100m	35.5	33.5			17.7	14.7	16.2	

Table Notes: Limits above 300 MHz are for information only. Reference standard: IEC 61156-5

Voltage

Voltage Rating
72 V DC

Mechanical Characteristics

Temperature

Operating	Installation
-30°C to +60°C	0°C To +50°C

Bend Radius

Stationary Min.	Installation Min.
23 mm (0.91 in)	46 mm

Max. Pull Tension: 130 N (29 lbf)

Bulk Cable Weight: 68 kg/km

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Dca
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Dca-s2,d2,a1
IEEE Compliance:	PoE: IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA 568.2-D
ISO/IEC Compliance:	ISO/IEC 11801-1
CENELEC Compliance:	EN 50173-1, Segregation class according EN50174-2 = a
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

Product Notes

Notes: Electrical values are expected performance based on cable testing and representative performance within a typical Belden system.

History

Update and Revision: Revision Number: 0.259 Revision Date: 05-31-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
NN01302.00500	White	Reel	500 m	8719605103642

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.