



**Product:** [NTCL12AA008YEA](#) 

Indoor tight buffered optical fiber distribution cable with Single LSZH jacket 8F SM G652.D, GB 31247 B1 rated

## Product Description

Indoor optical fiber distribution cable: 900µm LSZH tight buffer, aramid yarn reinforcing, Single LSZH jacket, 8 fibers, SM G652.D - GB 31247 B1 rated

## Technical Specifications

### Product Overview

Product Category:	Fiber Distribution Cable
Suitable Applications:	High degree of flexibility suitable for backbone, horizontal, inner and inter building installations; Excellent burning behavior performance LSZH(low smoke emission and low smoke toxicity) is ideal for the buildings with very high safety requirements

### Fiber Specifications

Fiber Type:	OS2, G.652.D
Fiber Core Diameter:	9 µm
Fiber Diameter:	125 µm
Fiber Buffer Material:	LSZH
Fiber Buffer Construction:	Tight buffer
Fiber Buffer Diameter:	900 µm
Fiber Count:	8
Fiber Color Coding:	TIA-598-D

### Outer Jacket Specifications

Strength Member:	Aramid Yarns
Jacket Material:	LSZH - Low Smoke Zero Halogen (Flame Retardant)
Nom. Diameter:	5.8 mm (0.23 in)
Outer Jacket Color:	Yellow

### Optical Characteristics

Wavelength	1310 nm	1550 nm
Max. Attenuation	0.36 dB/km	0.22 dB/km
Mode Field Diameter	8.8 µm	9.9 µm

### Mechanical Characteristics

Minimum Bend Radius During Installation:	20 x OD
Minimum Bend Radius During Operation:	10 x OD
Max. Tensile Strength During Installation:	660 N (150 lbf)
Max. Tensile Strength During Operation:	200 N (45 lbf)
Crush Resistance:	Max Crush Resistance During Installation: 1000N/100mm, Max Crush Resistance During Operation: 300N/100mm

### Mechanical Tests

Description	Tested Standard
Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E11
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1

Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1
Cable Max. Crush Resistance Installation (Short Term)	IEC 60794-1-21-E3
Cable Max. Crush Resistance Operation (Long Term)	IEC 60794-1-21-E3

Bulk Cable Weight:	35 kg/km (24 lbs/1000ft)
--------------------	--------------------------

## Temperature Range

Operating Temperature Range:	- 20°C to + 60°C
Storage Temperature Range:	- 20°C to + 60°C

## Standards and Compliance

Environmental Suitability:	Indoor
GB Compliance:	GB 31247
ISO/IEC Compliance:	IEC 60793-1-1/IEC 60794-1-1
European Halogen Free Standards:	IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 , IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment)

## Product Notes

Notes:	GB 31247 B1 (d0, t0, a1)
--------	--------------------------

## History

Update and Revision:	Revision Number: 0.37 Revision Date: 08-15-2025
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.