

Product: [OWL 3G](#) 

LTE Ethernet Gateway, Europe, VPN, GPS, Dual SIM, MicroSD



Product Description

Industry 4.0 and Industrial IoT Cellular Router and Gateway. Optimized for 3G applications with edge pre-computing. VPN and openly programmable and extendable Linux.

Technical Specifications

Product description

Type:	OWL 3G-S20TT9999209SDAHHXX.X.XX
Name:	OWL 3G
Description:	Industry 4.0 and Industrial IoT Cellular Router and Gateway. Optimized for 3G applications with edge pre-computing. VPN and open extendable Linux.
Part Number:	942145001
Port type and quantity:	2x Ethernet, 1x Antenna, 1x Diversity, 2x SIM, 1x Power
Country certification:	Europe (Austria, Belgium, Bulgaria, Croatia, Cyprus, Czech, Denmark, Estonia, Finland, France, Germany, Great Britain, Greece, Hungary, Ireland, Italy, Latvia, Lithuania, Luxembourg, Malta, Netherland, Poland, Portugal, Romania, Sweden, Slovakia, Slovenia, Spain), Iceland, Liechtenstein, Norway, Switzerland, Turkey

Product Life Cycle

Availability:	Discontinued -Last order date 12. November 2020
---------------	---

More Interfaces

SIM Cards:	2x 2FF (3V, 1.8V), only one active at a time, can be configured independently, automatic switch on connection failure
Ethernet:	2x Ethernet: 10/100 Mbit/s (RJ45)
Power Supply:	Via 2-pin terminal block 3.5mm (included)

Radio technology

Antenna connector:	2 x SMA Female (Cellular, Diversity)
Frequency band:	GSM/GPRS/EDGE (2G): 850/900/1800/1900 MHz, UMTS/HSDPA/HSUPA/HSPA+ (3G): 800/850/900/1900/2100 MHz
Transmission rate:	HSPA+: 14,4 Mbps Download, 5,76 Mbps Upload

Power requirements

Current consumption:	Reception: 2.3 W, GPRS: 3.5 W, UMTS: 5.5 W
Operating Voltage:	12 V DC to 24 V DC
Redundancy functions:	Dual VRRPv2 (with ping probes), Dual VRRPv3 (with ping probes), multiple routed interfaces (ping monitoring, failover and load balancing), PPPoE bridge mode

Diagnostics features

Monitoring:	Syslog (UDP) , SNMPv1/2c/3
-------------	----------------------------

Security features

Authentication:	User Management (local, RADIUS, TACACS+, mixed)
Stateful inspection firewall:	Static Firewall IPv4/IPv6 with Incoming and Forwarding Ruleset, DoS protection

Service

Other services:	DHCP Server (IPv4/IPv6, dynamic and static leases, IPv6 Prefix Delegation, DNS proxy) , DynDNS client , PPPoE , FTP server , E-Mail via SMTP , SMS (notifications and commands) , Telnet server
-----------------	---

Software

Operating system:	Custom embedded Linux with Busybox Shell
VPN:	OpenVPN, IPSec, GRE, L2TP, PPTP
Switching:	VLAN (via Scripting), tunneled VLANs (via Scripting) , IGMP
Management:	HTML5, SSH, SNMPv1/2c/3, Automatic configuration and firmware fetch from a web- or ftpserver, backup and restore with drag & drop
Diagnostics:	One click support report package, System log, Linux kernel log, reboot log, signal strength history (60 days), SSH linux shell, Signal strength LED indicators
Configuration:	Simple to edit text file configuration, HTTP, HTTPS, SMS, SSH, Telnet, 4 Configuration Profiles, automatic via web/ftp, SNMPv1/2c/3
Security:	HTTPS, SSH, Authentication with RADIUS or TACACS+, activate cellular interface with SMS, Ethernet 802.1X (EAP-PEAP/MsCHAPv2 or EAP-TLS)
Time synchronisation:	SNTP Client, SNTP Server
Routing:	Static unicast routing, Multinetting, IP masquerading, Port forwarding, Multiple routes with priority and load sharing, 1:1 NAT
Dynamic routing:	Dual VRRPv2 (with ping probes), Dual VRRPv3 (with ping probes), multiple routed interfaces (ping monitoring, failover and load balancing)

Ambient conditions

MTBF (MIL-HDBK 217F: Gb 25 °C):	67.2 Years
Degree of Protection when Installed:	IP30
Operating temperature:	-40-+70 °C
Storage/transport temperature:	-40-+85 °C
Relative humidity (non-condensing):	0-95 %

Mechanical construction

Dimensions (WxHxD):	42x114x81 mm
Weight:	280 g
Housing:	Metal
Mounting:	DIN Rail
Protection class:	IP30

Approvals

Safety of industrial control equipment:	EN 60950-1
Safety of information technology equipment:	EN 60950-1
Environmental:	EN 61000-6-2, EN 301 489, EN 61131 for use in automation environment
Radio:	EN 301 511, EN 300 440-2, EN 301 908(-1,-2,-13)

Scope of delivery and accessories

Accessories:	942042105 Indoor LTE Antenna , 942117001 50Ohm terminator for cellular antenna , 943662015 Rail Power Supply
Scope of delivery:	Device, DIN rail clip, power connector

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com
Certificates:	https://www.doc.hirschmann.com/certificates.html

History

Update and Revision:	Revision Number: 0.129 Revision Date: 03-06-2023
----------------------	--

Variants

Item #	Type
942145001	OWL 3G-S20TT9999209SDAHH01.0.

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.