

Product: RKWTS 4S-1027





M12 Power Single-Ended Cordset: Female, angled, 4-pin(3+PE), S-coded, shielded, blue body, 600 V AC/DC, 20A; PUR black cable, ca. 2,5mm²

Product Description

M12 Power Single-Ended Cordset: Female, angled, 4-pin(3+PE), S-coded, shielded, blue body, 600 V AC/DC, 20A; PUR black cable, 2.5 mm²

Technical Drawing





Technical Specifications

Face View

 Pin 1
 Pin 2
 Pin 3
 PE

 black 1
 black 2
 black 3
 green-yellow

Technical Data

Product Family:	Power Connector
Product Sub Family:	M12 Power
Brand:	Belden
Connector Type:	Cordset, single ended
Type of Contact / Gender:	female
Connector Design:	angled
Number of Pins:	4
Coding:	S
Shielding:	Shielded
Attachment Type:	Coupling Nut
Rated Voltage:	630 V
Rated Voltage (UL):	600 V
Rated Impulse Voltage:	6.0 KV
Operating Voltage:	600 V AC/DC
Rated Current*:	24 A
Rated Current (UL)*:	20 A

Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10^9 Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	-40 °C to +125 °C, notice derating
Protection Degree / IP Rating**:	IP65, IP67, IP69K
Design Standard:	IEC 61076-2-111
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Clearance / Creepage Distance:	DIN EN 60664-1 (2008/01); VDE 0110-1
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)

Materials

Contact Base Material:	CuNi
Contact Plating:	Cu/Au
Contact Bearer Material:	PBT GF
Contact Bearer Color:	black
Flammability Class (Contact Bearer):	UL 94 V-2
Molded Body Material:	TPE
Molded Body Color:	blue
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	CuZn
Attachment Plating:	Cu/Ni
O-Ring Material:	FKM

Additional Technical Data

Fastening Torque (Contact Screw):

M 12x1: (60-65) Ncm, hand-tight

Cable Data

1027
2.5 mm ²
≤ 8.2 Ω/km (at 20 °C)
4
> 4 x D
> 7.5 x D
> 10 M
Cu
PUR
black
ø 9.4 ±0.20 mm
PP
ø 2.55 mm
tinned copper braided screen
-40 °C to +90 °C (UL AWM 80°C)
-30 °C to +90 °C (UL AWM 80°C)
-40 °C to +125 °C
-20 °C to +60 °C
AWM: 20939
VDE 0482-332-1-2, DIN EN 60332-1-2 / IEC 60332-1 / UL VW-1, CSA FT1

Approvals

UL-File:	E497237
UL:	UL 2237; cULus
VDE:	No

Safety & Environmental Compliance		
RoHS Compliant:	yes	
Resistances		
Halogenfree:	DIN VDE 0472 T.815	

Oil Resistance:

HD 22.10 Appendix A, DIN EN 60811-404

Notes

Note Derating: * Notice derating Protection Degree / IP Rating Note: ** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.

Variants

Item #	Item Description
934850197	RKWTS 4S-1027/3 M
934850198	RKWTS 4S-1027/5 M
934850199	RKWTS 4S-1027/10 M
934850200	RKWTS 4S-1027/15 M

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.