



**Product:** [OWL LTE M12-S20T5A12221GTDBHHXX.X.XX](#) 

Life Cycle Status: Limited Availability/Passive

LTE Ethernet Gateway, Europe, M12, VPN, GPS, Dual SIM, Serial, IO, USB, MicroSD, Transportation (EN50155)

## Product Description

Transportation EN50155 Cellular Router and Gateway. Optimized for 4G applications with edge pre-computing. VPN and openly programmable and extendable Linux. VRRP for router redundancy. Dead reckoning for GPS even inside tunnels.

## Technical Specifications

### Product description

Type:	OWL LTE M12-S20T5A12221GTDBHHXX.X.XX
Name:	OWL LTE M12
Description:	Transportation EN50155 Cellular Router and Gateway. Optimized for distributed 4G applications with edge pre-computing. VPN and open extendable Linux. VRRP for router redundancy. Dead reckoning for GPS even inside tunnels.
Part Number:	942147002
Port type and quantity:	2x Ethernet, 2x Antenna, 1x GPS, 2x SIM, 1x Power, 4x I/O, 1x USB, 1x Serial, 1x MicroSD
Serial:	8-port M12 A-Coded (connector NOT included): RS232 , Serial2TCP , Serial2UDP
Country certification:	Europe (Austria, Belgium, Bulgaria, Croatia, Cyprus, Czech, Denmark, Estonia, Finland, France, Germany, Great Britain, Greece, Hungary, Ireland, Italy, Latvia, Lithuania, Luxembourg, Malta, Netherland, Poland, Portugal, Romania, Sweden, Slovakia, Slovenia, Spain), Iceland, Liechtenstein, Norway, Switzerland, Turkey
Hard disk space:	Can be extended with MicroSD (up to 64GB)

### Product Life Cycle

Life Cycle:	Limited Availability/Passive - the product is entering End of Life
Availability:	Limited
Last Order Date:	2022-10-31

### More Interfaces

USB interface:	1 x 5-pin M12 A-coded socket (connector NOT included)
SIM Cards:	2x 2FF (3V, 1.8V), only one active at a time, can be configured independently, automatic switch on connection failure
Ethernet:	2x Ethernet: 10/100 Mbit/s (M12 D-Coded)
Power Supply:	M12 A-coded 5-pin (connector NOT included)
Signaling contact:	8-port M12 A-Coded (connector NOT included): 2x Digital Input, 2x Digital Output

### Radio technology

Antenna connector:	3 x SMA Female (Cellular, Diversity, GPS)
Frequency band:	GPRS/EDGE (2G): 900(Band 8) /1800(Band 3) MHz, UMTS/HSPA+ (3G): 900(Band8) /2100(Band 2) MHz, LTE (4G): 800(Band 20) /900(Band 8) /1800(Band 3) /2100(Band 1) /2600(Band 7) MHz
Transmission rate:	LTE Category 4: 150 Mbit/s Download, 50 Mbit/s Upload
Additional radio features:	GNSS (GPS, GLONASS, Galileo, QZSS), Dead Reckoning

### Power requirements

Current consumption:	Idle 2.5 W, Average 4 W, Maximum 11 W
Operating Voltage:	12 V DC to 36 V DC, PoE PD on request
Power consumption:	4 to 11 W
Redundancy functions:	Dual VRRPv2 (with ping probes), Dual VRRPv3 (with ping probes), multiple routed interfaces (ping monitoring, failover and load balancing), PPPoE bridge mode

### Diagnostics features

Modules and components:	User modules pre-installed: GPS, User modules as separate download: GPS Dead Reckoning, Lua, Python, NodeRED
Monitoring:	Syslog (UDP) , SNMPv1/2c/3

### Security features

Authentication:	User Management (local, RADIUS, TACACS+, mixed)
Stateful inspection firewall:	Static Firewall IPv4/IPv6 with Incoming and Forwarding Ruleset, DoS protection

### Service

Other services:	DHCP Server (IPv4/IPv6, dynamic and static leases, IPv6 Prefix Delegation, DNS proxy) , DynDNS client , PPPoE , FTP server , E-Mail via SMTP , SMS (notifications and commands) , Telnet server
-----------------	---

### Software

Operating system:	Custom embedded Linux with Busybox Shell
VPN:	OpenVPN, IPSec, GRE, L2TP, PPTP
Switching:	VLAN (via Scripting), tunneled VLANs (via Scripting), IGMP
Management:	HTML5, SSH, SNMPv1/2c/3, Automatic configuration and firmware fetch from a web- or ftpserver, backup and restore with drag & drop
Diagnostics:	One click support report package, System log, Linux kernel log, reboot log, signal strength history (60 days), SSH linux shell, Signal strength LED indicators
Configuration:	Simple to edit text file configuration, HTTP, HTTPS, SMS, SSH, Telnet, 4 Configuration Profiles, automatic via web/ftp, SNMPv1/2c/3
Security:	HTTPS, SSH, Authentication with RADIUS or TACACS+, activate cellular interface with SMS, Ethernet 802.1X (EAP-PEAP/MsCHAPv2 or EAP-TLS)
Time synchronisation:	SNTP Client, SNTP Server, GPS
Routing:	Static unicast routing, Multinetting, IP masquerading, Port forwarding, Multiple routes with priority and load sharing, 1:1 NAT
Dynamic routing:	Dual VRRPv2 (with ping probes), Dual VRRPv3 (with ping probes), multiple routed interfaces (ping monitoring, failover and load balancing)

### Ambient conditions

MTBF (MIL-HDBK 217F: Gb 25 °C):	38 Years
Degree of Protection when Installed:	IP40
Operating temperature:	-40-+70 °C
Storage/transport temperature:	-40-+85 °C
Relative humidity (non-condensing):	0-95 %
Protective paint on PCB:	Yes (conformal coating)

### Mechanical construction

Dimensions (WxHxD):	203x62x127 mm
Weight:	960 g
Housing:	Metal
Mounting:	Wall mounting
Protection class:	IP40

### Approvals

Safety of industrial control equipment:	EN 60950-1
Safety of information technology equipment:	EN 60950-1
Environmental:	EN 61000-6-2, EN 301 489, EN 61131 for use in automation environment
Transportation:	EN 50155 (Onboard), EN 50121-4 (Trackside), EN 45545-2:2013 + A1:2015 HL3 (Fire)
Radio:	EN 301 511, EN 301 489(-1,-7,-24), EN 301 908(-1,-2,-13)

### Reliability

Guarantee:	60 months (please refer to the terms of guarantee for detailed information)
------------	---

### Scope of delivery and accessories

Accessories:	942042105 Indoor LTE Antenna , 942042108 Indoor GPS antenna , 942087001 Terminal cable M12 to DB9 , 933170100 M12 A-coded connector (Power/USB) , 934637655 Ethernet M12-D to RJ45 (4 meters) , 107521 Single-Ended M12-A (5 meters) for I/O or RS232 , 943662015 Rail Power Supply
Scope of delivery:	Device, Wall mount brackets

### Further Instructions

Product Documentation:	<a href="https://www.doc.hirschmann.com">https://www.doc.hirschmann.com</a>
Certificates:	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>

History

Update and Revision:	Revision Number: 0.155 Revision Date: 03-25-2025
----------------------	--

Variants

Item #	Type
942147002	OWL LTE M12-S20T5A12221GTDBHHXX.X.XX

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.