



Product: [P03044BF](#) 

TC-ER EPR(EPCV)/CPE, 3+G C #4+8 Str BC, EPCV Ins , Blk CPE Jkt, 600/1000V TC-ER 90C Dry/Wet SUN RES DIR BUR,OIL RES I/II,FT4

Product Description

TYPE TC-ER: 3 CONDUCTORS - 4 AWG TINNED CU CONDUCTORS WITH EPR(EPCV) VW-1 INSULATION, 8 AWG TINNED COPPER GROUND, FR FILLER REQUIRED, CPE JACKET.

Technical Specifications

Product Overview

Suitable Applications:	Power and Control Applications up to 600/1000V Class 1 Division 2 Hazardous Locations; Recommended Cable
------------------------	--

Physical Characteristics (Overall)

Conductor

Element	AWG	Material	No. of Conductors
Conductor(s)	4	BC - Bare Copper	3
	8		1

Conductor Count:	4
------------------	---

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
EPR or EPCV - Ethylene Propylene Rubber	0.120 in	0.031 in
No Insulation		

Color Chart

Color
Black & Numbered

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
CPE - Chlorinated Polyethylene	0.808 in	0.063 in	Yes

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
0.26 ohms/1000ft

Current

Max. Recommended Current [A]
95 Amps per Conductor at 30°C

Voltage

UL Description	Voltage Rating [V]
TC-ER	600/1000 V (Type TC-ER)

Temperature Range

UL Temperature Rating:	90°C Dry, 90°C Wet
Operating Temperature Range:	Wet/Dry: -40°C to 90°C

Dry Temp Range:	-30°C To +90 °C
-----------------	-----------------

Mechanical Characteristics

Bulk Cable Weight:	597 lbs/1000ft
Maximum Recommended Pulling Tension:	1135 lbs
Minimum Bend Radius During Installation:	3.2 in

Standards

NEC/(UL) Compliance:	TC-ER, XHHW-2
----------------------	---------------

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL 1685 UL loading
------------------	--------------------

History

Update and Revision:	Revision Number: 0.5 Revision Date: 10-08-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.