



**Product:** [PDU-12303](#)

PDU Basic V Upg 230/400V 16A 3P+N+E (24)LC13(6)LC19

### Product Description

PDU, Basic Upgradeable, 16A, 230/400V WYE, 11.0kW, Vertical, (24) Locking IEC C13, (6) Locking IEC C19, 3m power cord with 3P+N+E (IP44)

### Technical Specifications

#### Application

Environmental Space:	Indoor
Power Distribution Type:	Basic Upgradeable
Monitoring:	None. (upgradeable with HSMD module)

#### Construction and Dimensions

Width:	51 mm
Depth:	51 mm
Length:	1683 mm

#### Electrical Characteristics

Input voltage:	200-240/346-415 V WYE
Rated Current*:	16 A x 3 Phase WYE
Input frequency:	50/60 Hz
VA per Input (Load Capacity):	11.0 kW

#### Mechanical Construction

On-Off Switch:	No
Plug Type:	IEC60309 3P + N + E, 16A, 230/400V, Splashproof IP44
Quantity Of Inputs:	1
Power Entry Location:	Bottom Front
Total Receptacle:	30
Receptacle 1 Type:	IEC C13 Locking
Receptacle 1 Quantity:	24
Receptacle 1 Quantity per Breaker:	0
Receptacle 1 Style:	Individual
Receptacle 1 Voltage per Receptacle:	230 V
Receptacle 2 Type:	IEC C19 Locking
Receptacle 2 Quantity:	6
Receptacle 2 Quantity per Breaker:	0
Receptacle 2 Style:	Individual
Receptacle 2 Voltage per Receptacle:	230 V
Cord Length:	3 m
Type of Cordage:	2.5 mm <sup>2</sup> H07RN-F

#### Mechanical Characteristics

Mounting:	Vertical
Toolless Mounting Hardware Center to Center Spacing:	1556mm and 1645mm

## Environmental and Overall Characteristics

Ambient Temperature (operation), max:	45
Finish:	Powder
Material:	Steel
Color:	Black
Weight:	6.8 kg

## Standards

EU CE Mark:	Yes
EU Directive 2011/65/EU (RoHS 2):	Compliant
CENELEC Compliance:	EN 55032, EN 55024

## Related Part Numbers

Part Number:	PDU-12303
Packaging:	Individually boxed

## Variants

Item #	Color
PDU-12303	Black

Update and Revision:	Revision Number: 0.13 Revision Date: 03-30-2023
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.