




Product: [PDUI-X512C12I](#)

PDU Basic St V 230/400V 32A 3P+N+E (12)C13(12)C19

Product Description

PDU Basic Standard, Vertical, 230/400V 32A 3P+N+E (12)C13(12)C19

Technical Drawing



Technical Specifications

Application

Environmental Space:	Indoor
Power Distribution Type:	Basic Standard

Construction and Dimensions

Width:	51 mm
Depth:	61.2 mm
Length:	1830 mm

Electrical Characteristics

Input voltage:	230/400V WYE
Rated Current*:	32 A x 3 Phase WYE
Input frequency:	50/60Hz
VA per Input (Load Capacity):	22.0kW

Mechanical Construction

On-Off Switch:	Breaker/Switch Combination
Plug Type:	IEC60309 3P + N + E, 32A, 230/400V, Splashproof IP44
Quantity Of Inputs:	1
Power Entry Location:	Front Bottom
Receptacle 1 Type:	IEC C13
Receptacle 1 Quantity:	12

Receptacle 1 Quantity per Breaker:	2
Receptacle 1 Voltage per Receptacle:	230 V
Receptacle 2 Type:	IEC C19
Receptacle 2 Quantity:	12
Receptacle 2 Quantity per Breaker:	2
Receptacle 2 Voltage per Receptacle:	230V
Cord Length:	3 m
Type of Cordage:	5 x 6mm ² / H07RN-F

Mechanical Characteristics

Mounting:	Vertical
Toolless Mounting Hardware Center to Center Spacing:	1556 & 1645 mm

Environmental and Overall Characteristics

Ambient Temperature (operation), max:	60
Finish:	Powder coat
Material:	Steel
Color:	Black
Weight:	7 kg

Standards

EU CE Mark:	Yes
EU Directive 2011/65/EU (RoHS 2):	Compliant

Related Part Numbers

Part Number:	PDUI-X512C12I
Packaging:	Individually boxed

Variants

Item #	Color
PDUI-X512C12I	Black

Update and Revision:	Revision Number: 0.7 Revision Date: 09-02-2022
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.