



PDU Meter St Disp V 230V 32A 2P+E (30)C13(6)C19

PDU, Metered Standard, 32A, 230V, 7.3kW, Vertical, (30) IEC C13 (6) IEC C19, 3 m power cord 2P+E (IP44)

Technical drawing of the Belden 63039 Plug, showing top, side, and perspective views with dimensions and callouts.

Top View Dimensions:

- Overall length: 1683
- Width: 51
- Callout A points to the center of the plug.

Side View Dimensions:

- Height: 56.2

Perspective View Dimensions:

- Ratio: A (0.41 : 1)
- Callout A points to the front of the plug.

Callouts and Details:

- c/w Toolless & End Fixing Kit**: Points to the end of the plug.
- BS 63039 PLUG**: Points to the plug itself.
- Dimensions in mm unless stated otherwise**: Note at the bottom.

Belden Logo and Part Information:

BELDEN

Part No. TBC
 Description 22 AWG Wire with 20 x C118 A in C119 Unswitched with 20x Cord-to-RGB Plug - Local Power Meter

Application

Environmental Space:	Indoor
Power Distribution Type:	Metered Standard
Monitoring:	Digital Power Meter
Input Monitoring:	A,V,W,PF

Overall Width:	51 mm
Depth:	56 mm
Overall Length:	1683 mm

Input voltage:	200-240V
Current Rating:	32 A
Input frequency:	50/60 Hz
VA per Input (Load Capacity):	7.3 kW

On-Off Switch:	Breaker/Switch Combination
Plug Type:	IEC60309 2P + E, 32A, 250V, Splashproof IP44
Quantity Of Inputs:	1
Receptacle 1 Type:	IEC C13

Receptacle 1 Quantity:	30
Receptacle 1 Quantity per Breaker:	15
Receptacle 1 Voltage per Receptacle:	230 V
Receptacle 2 Type:	IEC C19
Receptacle 2 Quantity:	6
Receptacle 2 Quantity per Breaker:	3
Receptacle 2 Voltage per Receptacle:	230 V
Cord Length:	3 m

Mechanical Characteristics

Mount Type:	Vertical
-------------	----------

Environmental and Overall Characteristics

Ambient Temperature (operation), max:	60
Finish:	Powder coat
Material:	Steel
Color:	Black

Standards

EU CE Mark:	Yes
EU Directive 2011/65/EU (RoHS 2):	Compliant
CENELEC Compliance:	EN 62368

Related Part Numbers

Part Number:	PDUJ-V530C06I
Packaging:	Individually boxed

Variants

Item #	Color
PDUJ-V530C06I	Black

Update and Revision:	Revision Number: 0.7 Revision Date: 06-13-2022
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.