Belden



Product: RMG1C120

RailTuff™ Medium wall cable 1800V 1 C 120 mm² Str TC,XLPO Ins

Product Description

RailTuff™ Medium wall cable 1800V 1 Core 120 mm² Stranded Tinned Copper, XLPO Insulation

Technical Specifications

Product Overview

Suitable Applications:	Applicable for fixed or moderate flexing wiring inside Railway Rolling Stock like High-Speed Trains (CRH, Shinkansen, ICE, TGV), Metro, locomotives, and trolley buses, etc

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Stranding Class	Material
Conductor(s)	1	120 mm²	551x0.50 mm	Class 5	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code
Conductor(s)	XLP, XLPO, XLPE	2.2 mm (0.087 in)	White, Black

Overall Cable Diameter (Nominal):	19.8 ± 0.40 mm

Electrical Characteristics

Electricals

Max. Conductor DCR
0.164 Ohm/km (0.0500 Ohm/1000ft)

Electricals Table Notes:	D.C. stability at 4.5kVdc in 3% NaCl solution at (85±2)°C for 240h : No breakdown

Voltage

Voltage Rating	Breakdown Voltage
1800/3000V	6.5kVac/5min

Voltage Rating Table Notes:	Dielectric strength on core in water for 1 hour (kVac): 10

Mechanical Characteristics

Temperature

Operating
-40°C to +90°C

Bend Radius

Stationary Min.	Installation Min.
99 mm (3.9 in)	79 mm (3.1 in)

Bend Radius Table Notes:	Elongation test at -40:Elongation at break 30 %
Bulk Cable Weight:	1227 kg/km (824.5 lbs/1000ft)

Standards and Compliance

Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-24
ISO/IEC Compliance:	IEC 60228

CENELEC Compliance:	EN 50264-3-1, EN 45545-2
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = HCl+HBr ≤ 0.5%, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
Other Standard Compliance(s):	TJ/CL 313

Product Notes

Notes:	EMEA PN: RMG1C120;

History

Update and Revision:	Revision Number: 0.25 Revision Date: 10-07-2026

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.