



Product: [PP-1U-4DC](#)

Empty Panel for Belden 96-Fiber PatchPro System



Product Description

96 Fiber System Empty Panel 1U Up to 4 LC Double Cassettes

Technical Specifications

Physical Specifications

Max Capacity:	4 LC Double Cassette, each LC Double Casette has 24 Fiber
---------------	---

Temperature Range

Operating Temperature Range:	-40 °C to +85 °C
Storage Temperature Range:	-50 °C to +100 °C

Product Material

Materials

Description	Material	Color	Type
Cold-rolled steel with nickel plating for corrosion resistance and strength	SPCC Steel (1.5 mm)	Metallic Silver (Nickel)	Patch Panel Body
Flame-retardant ABS plastic (UL 94V-0), lightweight and impact-resistant	ABS 94V-0	Black	Port Bracket
Standard rack-mounting screws for 19" installation	Steel, Zinc plated	Silver	Mounting Screws
Belden logo printed on front panel	Ink/Screen print	White	Front Logo/Marking

Related Part Numbers

Included Parts:	a. Port numbering label card x 8 b. Head machine screw x 4 c. Installation Guide x 1
Related Parts:	PPLSMOM, PPLAMPOM, PPL3MPOM, PPL4MPOM, PPL5MPOM PPLSMPOM-ALT, PPLAMPOM-ALT, PPL3MPOM-ALT, PPL4MPOM-ALT, PPL5MPOM-ALT PPFOUK-D PP range fiber patch cords

Product Notes

Packaging:	1 set per package
------------	-------------------

History

Update and Revision:	Revision Number: 0.15 Revision Date: 09-30-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.