



Product: [RMS-PCAUxx41xxxxM](#)

ProRMS Unshielded, Cat6A, LSZH Jacket, Copper Patch Cord



Product Description

ProRMS Unshielded, Cat6A, LSZH Jacket, TIA 568B, Copper Patch Cord

Technical Specifications

Physical Characteristics (Overall)

Inner Jacket

Color

Blue

Wiring Scheme: TIA 568B

Connectors

Materials

Description	Material
Plug Housing	PC - Polycarbonate, UL 94 V-2 rated
Contact Blade	Phosphor bronze plated with 50u" gold over 100u" nickel undercoat
Cable Conductor Type	Stranded Copper wire

Construction and Dimensions

Cable Type: Unshielded

Electrical Characteristics

Insulation Resistance:	100 Megaohms
Max Contact Resistance:	20 mOhm
Table Notes:	Dielectric withstanding : 1000 volts rms,1 min.(60Hz)

Mechanical Characteristics

Flex Cycle Rating: 500 Cycles

Standards

ISO/IEC Compliance:	IEC 60603-7, IEC 11801-1
TIA/EIA Compliance:	TIA 568.2-D
Other Standards:	IEC 61156-5, ISO/IEC 11801

Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2): Yes

Related Part Numbers

Variants

Item #	Color	Length
RMS-PCAUCC413601M	Blue	1 m
RMS-PCAUCC413602M	Blue	2 m

RMS-PCAUCC413603M	Blue	3 m
RMS-PCAUCC413605M	Blue	5 m
RMS-PCAUIC413601M	Blue	1 m
RMS-PCAUIC413602M	Blue	2 m
RMS-PCAUIC413603M	Blue	3 m
RMS-PCAUIC413605M	Blue	5 m

History

Update and Revision:	Revision Number: 0.21 Revision Date: 09-09-2022
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.