



Product: [PPCUUK](#)



PPRO CU Panel Pannel Mount Antenna Upgrade Kit (legacy)

Product Description

PPRO Copper Panel Upgrade RFID Antenna Kit

Technical Specifications

Product Overview

Suitable Applications:	Horizontal and building cabling for Intelligent (RFID based) Patching. Support current and future Category 6a and 6 applications, such as: 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
------------------------	---

Physical Characteristics (Overall)

Height:	10 mm
Width:	433 mm
Depth:	2 mm
Packaging:	Individually packaged in a box.

Connectors

Materials

Description	Material	Color
RFID antenna	24 RFID antennas	Black
LED	24 LEDs	

Construction and Dimensions

Max Capacity:	1 Panel
---------------	---------

Electrical Characteristics

Current Rating:	1.500 A
-----------------	---------

Temperature Range

Storage Temperature Range:	-20°C To +85°C
Operating Temperature Range:	0°C To +40°C

Standards

TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568-C.3
---------------------	-----------------------------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes
EU CE Mark:	Yes
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Related Parts:	PatchPro Connectivity; PPC6AUR, PPC6ASR, PPC6AUC, PPC6ASC
----------------	---

Variants

Item #	Color	Packaging
PPCUUK	Black	Individually packaged in a box.

History

Update and Revision:	Revision Number: 0.42 Revision Date: 05-31-2023
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.