



**Part Number:** PPRO PP 1U 48F OM4 SD MPO ALT

PatchPro 48-port SC OM4 iPLM Ready MPO Alternate Panel Set (Polarity B)

**Product Description**

PatchPro 48-port SC OM4 iPLM Ready MPO Alternate Panel Set (Polarity B)

**Technical Specifications**

**Product Overview**

Suitable Applications:	Horizontal and building cabling for Intelligent (RFID based) Patching. Support current and future Category 6a and 6 applications, such as: 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
------------------------	---

**Construction**

Height:	45 mm
Width:	485 mm
Depth:	300 mm

**Physical Specifications**

Max Capacity:	24 Duplex SC Ports
---------------	--------------------

**Mechanical Characteristics**

Front Connection:	Flush
Footprint/Type:	SC

**Temperature Range**

Operating Temp Range:	-10°C To +60°C
Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-10 to 75°C

**Product Material**

**Materials**

Description	Material	Color
Panel	Zinc-coated Steel	Black
Body of Fiber Adapter	Plastic	Erica Violet

**Standards**

Telecommunications Standards:	ISO/IEC 11801-1:2017(Ed.3) ; TIA 568-C.3; EN 50173:2018
EU Directive 2011/65/EU (ROHS II):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2016-12-21
MII Order #39 (China RoHS):	EUP 50

**Additional Notes**

Packaging:	Individually packaged in a box.
Related Parts:	PatchPro Connectivity, MPO Trunk cables, Fiber patch cords

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.