



Product: [RS 100M-S4677](#)

1-1/8" - Male 0° | #Contacts: 10 | 600 V | Cable: Yellow (TPE); 16 AWG; US | cURus

Product Description

Single-Ended Cordset | 1-1/8" - Male Straight | #Contacts: 10 | 600 V / 7 A | Cable: TPE Yellow; 10x16 AWG; US | UL 2238; cURus

Technical Specifications

Face View

Pin 1	Pin 2	Pin 3	Pin 4	Pin 5	Pin 6	Pin 7	Pin 8	Pin 9	Pin 10
orange	blue	white/black	red/black	green/black	orange/black	red	green	black	white

Technical Data

Product Family:	Power Connector
Side 1 Product Sub Family:	1-1/8" (9, 10, 12, 19 contacts)
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Connector Sub Type:	Single-ended; Male Cordset
Side 1 Type of Contact/Gender:	Pin Contact / Male
Connector Design:	1-1/8" Male 10 Pole 0°
Number of Pins:	10
Coding, Side 1:	A
Shielding Type:	Unshielded
Attachment Type:	Male Thread (coupling screw)
Replacement for:	PF_RS 100M-699
Voltage Rating:	600 V
Rated Voltage (UL):	600 V
Operating Voltage:	540 V AC/DC
Current Rating:	7 A
Rated Current (UL)*:	Power 7 A Signal 7 A
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10 ⁹ Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 40 °C to + 90 °C
Protection Degree / IP Rating**:	IP65, IP67
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)

Materials

Contact Base Material:	Brass (CuZn)
Side 1 Contact Plating:	Copper-Silver-Gold-Alloy (Cu/Ag/Au)
Contact Bearer Material:	Thermoplastic polyurethane (TPU)
Contact Bearer Color:	Yellow
Flammability Class (Contact Bearer):	UL 94 HB

Molded Body Material:	Thermoplastic polyurethane (TPU)
Molded Body Color:	Yellow
Flammability Class (Molded Body):	UL 94 HB
Housing Color:	Yellow
Attachment Material:	Aluminum (Al)
Attachment Plating:	Anodized; Black

Additional Technical Data

Fastening Torque (Attachment):	1-1/8" 70 Ncm, hand-tight
Mating Connectors / Fitting to:	RKF 100M-699

Cable Data

Cable Number:	S4677
Conductor Size:	16 AWG
Number of Wires:	10
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 5 mio
Conductor Material:	Cu
Cable Jacket Material:	Thermoplastic Elastomers (TPE)
Cable Jacket Color:	Yellow
Cable Diameter D:	Ø 12.75 mm [0.502"]
Wire Insulation Material:	Polyvinyl Chloride (PVC)
Insulated Wire Diameter:	Ø 2.56 mm [0.101"]
Ambient Temperature (Fixed Installation):	- 30 °C to + 90 °C
Ambient Temperature (Flex Installation):	+ 5 °C to + 90 °C
UL Cable Type:	UL: NEC Type TC-ER (UL 1277)
Flammability Class (Cable Jacket):	UL 1685, CSA FT4, IEEC 1202
Cable Characteristics:	Flexibility: Excellent Abrasion Resistance: Very Good Chemical Resistance: resists water, oils, greases, acids, alkalis, and solvents Flame Retardance: Good Halogen-Free: No Mechanical Durability: Good (resists impact, tear, and flex) Environmental Suitability: outdoor, oily, wet, or rough environments

Approvals

UL-File:	E315587
UL:	UL 2238; cURus

Safety & Environmental Compliance

REACH:	Compliant
RoHS Compliant:	Yes

Resistances

Halogenfree:	No
Oil Resistance:	Yes
UV Resistance:	Yes

Notes

Note Derating:	* Notice derating
Protection Degree / IP Rating Note:	IP Rating tested according to IEC standard using combination of a Hirschmann or Lumberg Automation connector mounted and locked

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.