



Product: [PPO PC OS2/A LCDX LCDX LSZH](#)

PatchPro Fiber Optic Patch Cord LC Duplex - LC Duplex, OS2/APC, with RFID chip, LSZH, Yellow Jacket

Product Description

PatchPro Fiber Optic Patch Cord LC Duplex - LC Duplex, OS2/APC, with RFID chip, LSZH, Yellow Jacket

Technical Specifications

Product Overview

Suitable Applications:	PatchPro Intelligent Patching Management Solutions, Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

Fiber Specifications

Fiber Type:	OS2
-------------	-----

Physical Specifications

Measurement

Packaging
Individually packaged in a sealed plastic bag.

Mechanical Characteristics

Maximum Insertion Loss:	0.25 dB
Typical Insertion Loss:	0.12 dB
Minimum Reflectance @ 1550nm:	-60 dB

Temperature Range

Operating Temperature Range:	-20°C to +60°C
Storage Temperature Range:	-15°C to +50°C

Product Material

Materials

Description	Material	Color
Boot	Rubber	Green
Clip for Duplex Connector	Plastic	Transparent
Connector Body	Plastic	Green
Ferrule	Ceramic	
RFID Transponder	13.56 MHz read/write, Factory programmed unique cord ID, According to ISO 15696	

Standards and Compliance

Environmental Space:	Indoor
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568-C.3
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Variants

Item #	Color	Put-Up Type	Length	EAN
PPOPAL.001	Yellow	Bag	1 m	8719605123428

PPOPAL.002	Yellow	Bag	2 m	8719605123435
PPOPAL.003	Yellow	Bag	3 m	8719605123442
PPOPAL.005	Yellow	Bag	5 m	8719605123459

Product Notes

Related Parts:	PatchPro Fiber panels, PatchPro connectivity
----------------	--

History

Update and Revision:	Revision Number: 0.55 Revision Date: 11-21-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.