



Product: [REVConnect Angled Panel 48P](#)

REVConnect Patch Panel, Empty, Angled, 2U, 48P

Product Description

REVConnect Patch Panel, Empty, Angled, 2U, 48 Ports

Technical Specifications

Product Overview

Suitable Applications:	For use with REVConnect Modular Jacks
------------------------	---------------------------------------

Physical Characteristics (Overall)

Height:	3.470 in
Width:	19.000 in
Depth:	5.830 in
Front Connection:	Angled
Packaging:	Individually packaged in a cardboard box.
Weight:	2.380 lbs.

Connectors

Materials

Description	Material	Color
Panel	Steel	Black/White
Frame	PC/ABS	Black/White
Management Bar	Steel	Black
Clear Window	Polycarbonate	Transparent

Construction and Dimensions

Max Capacity:	48 Connectors
---------------	---------------

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	KeyConnect
-----------------	------------

Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Related Part Numbers

Related Parts:	REVConnect Modular Jacks, REVConnect 10GXS, 10GXW, 3600, 2400, 1200 Systems
----------------	-----------------------------------------------------------------------------

Variants

Item #	Color	UPC
RVMPPA2U48BK	Black	611589238021
RVMPPA2U48WH	White	611589238038

Product Notes

Included Parts:	4 Frames; 4 Clear Windows; 1 Label Card; 1 Rear Cable Management Bar; 4 Screws (10x32); 4 Screws (12x24); 2 Velcro Straps; 2 Installation Guides (English and French)
Notes:	For proper installation, refer to Installation Guide PX106520 included with the product, or visit our website at http://www.belden.com

History

Update and Revision:	Revision Number: 0.12 Revision Date: 12-15-2021
----------------------	-------------------------------------------------

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.