



**Product:** [REVConnect Bulk Pack of Cores](#)

REVConnect Core Pack, Bulk Pack of 50 - select below appropriate core part number fitting the used cable

**Product Description**

REVConnect Core Pack, Bulk Pack of 50. Used to terminate REVConnect Jacks and Plugs - Compatible for Insulated wire diameter 0.9mm up to 1.3mm or 1.3mm up to 1.45mm

**Technical Specifications**

**Product Overview**

Suitable Applications:	Terminate REVConnect Jacks and Plugs
------------------------	--------------------------------------

**Physical Characteristics (Overall)**

Packaging:	Bulk 50x core cable managers and caps packaged in a resealable plastic bags
Weight:	0.18 lbs

**Connectors**

**Materials**

Description	Material
Connector	PBT UL94V-0

**Temperature Range**

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

**Mechanical Characteristics**

Footprint/Type:	KeyConnect
Body Attachment Method:	Compression
Tool Compatibility:	REVConnect Termination Tool (p/n RVUTT01)
Contact Attachment Method:	Insulation Piercing

**Applicable Environmental and Other Programs**

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes

**Related Part Numbers**

**Variants**

Item #	Color	Packaging	Insulated Wire Diameter
RVUECOGY-B50	Gray	Bag of 50	1.3mm up to 1.45mm
RVUCOEW-B50	White	Bag of 50	0.9mm up to 1.3mm

**Product Notes**

Notes:	Insulation O.D. Range core = 0.90 to 1.30 mm & Insulation O.D. Range core = 1.30 to 1.45 mm, Cable Jacket O.D. Max = 9.3 mm
--------	---

**History**

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.