



**Product:** [REVConnect WM Cable Mgmt Chan.](#)

## REVConnect Wall-Mount Cable Management Channel

### Product Description

The REVConnect Wall-Mount Cable Management Channel is designed for use with the REVConnect Wall-Mount kits

### Technical Specifications

#### Product Overview

Suitable Applications:	IBDN System 4800,3600,2400,1200,10GX
------------------------	--------------------------------------

#### Physical Characteristics (Overall)

Height:	15.175 in
Width:	8.11 in
Depth:	9.244 in
Packaging:	Individually packaged in a cardboard box.
Weight:	5.4 lbs

#### Connectors

#### Materials

Description	Material	Color
Module	Steel	Black
Cable Support	Lexan	Black
Door	Aluminum	Silver

#### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

#### Standards

UL Rating:	UL1863
------------	--------

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes

#### Flammability, LSOH, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

#### Related Part Numbers

Related Parts:	REVConnect wall termination kit, REVConnect wall connector mount, REVConnect wall cable dressing module, REVConnect cable management channel, REVConnect wall horizontal channel kit
----------------	--

#### Variants

Item #	Color	UPC
RVUPCMC	Black	611589237956

## Product Notes

Included Parts:	2 Screws #8-32; 8 Velcro cable tie; 1 Installation guide; 1 Grommet; 1 Plunger
Notes:	Refer to Installation Guide PX106710 (English) or visit our web site at <a href="http://www.belden.com">http://www.belden.com</a>

## History

Update and Revision:	Revision Number: 0.27 Revision Date: 11-17-2022
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.