

Product: [RJ45I-MASV86-CAT6](#) 


Field Attachable | RJ45 | CAT 6



Product Description

RJ45 | Field Attachable | Male Plug | Angled | CAT 6 | Shielded

Technical Drawing



Technical Specifications

Face View

Pin 1	Pin 2	Pin 3	Pin 4	Pin 5	Pin 6	Pin 7	Pin 8
T568A Green White / T568B orange white	T568A green / T568B orange	T568A orange white / T568B green white	blue	blue white	T568 A orange / T568B green	brown white	brown

Technical Data

Product Family:	Data Connector
Side 1 Product Sub Family:	RJ45 Ethernet
Brand:	Belden
Connector Type:	Field attachable
Side 1 Type of Contact/Gender:	Spring Contact / Male
Connector Design:	Field Attachable RJ45 Angled
Number of Pins:	8
Coding, Side 1:	RJ45
Shielding Type:	Shielded
Attachment Type:	Plug
Voltage Rating:	63 V
Operating Voltage:	60 V DC
Current Rating:	1.5 A
Rated Current (UL)*:	1.5 A
Rated Current (CSA)*:	1.5 A
Data Transmission Type:	CAT 6

Data Transmission Rate:	1 Gbit/s
Insulation Resistance:	500 MΩ
Mating Cycles:	≥750
Type of Connection:	IDC
Cross Section:	AWG 22-26
Suitable Cables:	Outer cable diameter 6.00-8.00mm
Operating Temperature (UL):	-40 °C to +85 °C
Protection Degree / IP Rating**:	IP20

Materials

Contact Base Material:	Phosphor Bronze alloy (CuSnP)
Side 1 Contact Plating:	Gold (Au)
Contact Bearer Color:	Black
Housing Material:	Zinc-alloy (Zn)
Housing Color:	Metallic
Cable Gland Material:	metal

Additional Technical Data

Fastening Torque (Cable Gland):	hand-tight
---------------------------------	------------

Approvals

UL-File:	E77103
UL:	UL 1863; cURus
CSA:	Yes, via UL

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Protection Degree / IP Rating Note:	IP Rating tested according to IEC standard using combination of a Hirschmann or Lumberg Automation connector mounted and locked
-------------------------------------	---

Variants

Item #	Item Description
935316102	RJ45I-MASV86-CAT6

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.