





Product: [RK 30-619](#)

7/8" - Female 0° | #Contacts: 3 | 300 V | Cable CPE YE, 18 AWG, AUTO | cURus

Product Description

7/8" Molded Cordset Female Straight | #Contacts: 3 | 300 V / 8 A | Cable CPE Yellow, 3x18 AWG, AUTO | cURus 2238

Technical Drawing



Technical Specifications

Technical Data

Product Family:	Power Connector
Product Sub Family:	7/8" (2, 3, 4, 5, 6 contacts)
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Type of Contact / Gender:	Socket Contact / Female
Connector Design:	Straight (0°) Body w/ Internal Thread Coupling Nut
Number of Pins:	3
Shielding:	Unshielded

Attachment Type:	Round Coupling Nut
Rated Voltage:	300 V
Rated Current*:	8 A
Ambient Temperature (Operation)*:	- 40 °C to + 90°C
Protection Degree / IP Rating**:	IP65, IP67, NEMA 6P

Materials

Contact Base Material:	Brass (CuZn)
Contact Plating:	Gold over Silver (Au / Ag)
Contact Bearer Material:	Thermoplastic polyurethane (TPU)
Contact Bearer Color:	Yellow
Molded Body Material:	Thermoplastic polyurethane (TPU)
Molded Body Color:	Yellow
Attachment Material:	Aluminum (Al), Anodized Black

Cable Data

Cable Number:	619
Conductor Size:	18 AWG
Number of Wires:	3
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Conductor material:	Cu
Flammability Class (Cable Jacket):	FT-2
Cable Characteristics:	See downloads tab for details

Approvals

UL-File:	E315587
----------	---------

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Note Derating:	* Notice derating
Protection Degree / IP Rating Note:	IP Rating tested according to IEC standard using combination of a Hirschmann or Lumberg Automation connector mounted and locked

Variants

Item #	Item Description	Cable Length
500000001	RK 30-619/6F	6 ft
500000025	RK 30-619/12F	12 ft
500001038	RK 30-619/15F	15 ft
500000072	RK 30-619/20F	20 ft
500001040	RK 30-619/30F	30 ft

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.