

**Product:** [RSMWVS-4D-0467](#)




M8 pigtail, PROFINET (Fast Ethernet 100 Mbit/s), Cat 5e, shielded, male, 4 poles, D coded, angled, PUR green cable, AWM 20549, 48 V AC / 60 V DC, 4 A / 0.5 A UL rated, IP65, IP67

**Product Description**

M8 pigtail for PROFINET applications, Fast Ethernet Cat 5e up to 100 Mbit/s, shielded, 4 pole, D coded, male to male, angled, PUR green cable, AWM 20549,  $\varnothing 6.5 \pm 0.20$  mm, conductor size 2x2x0.34 mm<sup>2</sup>, 48 V AC / 60 V DC operating voltage, rated current 4 A, suited for IP65 and IP67 environment

**Technical Drawing**



**Technical Specifications**

**Face View**

Pin 1	Pin 2	Pin 3	Pin 4
yellow	white	orange	blue

**Technical Data**

Product Family:	Data Connectors
Side 1 Product Sub Family:	M8 4D
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Side 1 Type of Contact/Gender:	Male
Connector Design:	Angled
Number of Pins:	4
Coding, Side 1:	D
Shielding Type:	Shielded
Attachment Type:	Coupling Screw
Voltage Rating:	60 V
Rated Voltage (UL):	30 V
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	48 V AC / 60 V DC
Current Rating:	4 A
Rated Current (UL)*:	0.5 A

Data Transmission Type:	Fast Ethernet Cat5e
Data Transmission Rate:	100 Mbit/s
Side 1 Contact Resistance:	10 mOhm
Insulation Resistance:	> 10 <sup>8</sup> Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 25 °C - + 90 °C
Protection Degree / IP Rating**:	IP65, IP67
Side 1 Design Standard:	IEC 61076-2-114
Side 1 Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)

## Materials

Contact Base Material:	CuSn
Side 1 Contact Plating:	Cu/Au
Contact Bearer Material:	PA
Contact Bearer Color:	Black
Molded Body Material:	TPU
Molded Body Color:	Black
Housing Material:	TPU
Housing Color:	Black
Attachment Material:	CuZn
Attachment Plating:	Nickel-plated

## Additional Technical Data

Fastening Torque (Attachment):	M 8x1: 20 Ncm, hand-tight
--------------------------------	---------------------------

## Cable Data

Cable Number:	467
Conductor Size:	2x2x0.34 mm <sup>2</sup>
Number of Wires:	4
Minimal Bending Radius (Fixed Inst):	5 x D
Minimal Bending Radius (Flexible Inst):	10 x D
Conductor Material:	Cu
Cable Jacket Material:	PUR
Cable Jacket Color:	green
Cable Diameter D:	ø 6.5 ±0.20 mm
Wire Insulation Material:	PE
Insulated Wire Diameter:	ø 1,63 ±0.05 mm
Overall Shield (Cable):	Cu-ETP1 tinned
Foil shield:	AL-PETP
Ambient Temperature (Fixed Installation):	- 25 °C - + 90 °C
Ambient Temperature (Flex Installation):	-25 °C - +60 °C
Ambient Temperature (Drag Chain Inst):	- 5 °C - + 60 °C
UL Cable Type:	AWM: 20549
Flammability Class (Cable Jacket):	FT-2
Cable Characteristics:	Exclusion of dangerous materials
Core Colors:	quad: white & blue & yellow & orange

## Approvals

UL-File:	E469096
UL:	UL 1863; cULus

## Safety & Environmental Compliance

RoHS Compliant:	yes
-----------------	-----

## Resistances

Halogenfree:	IEC 60754-1
--------------	-------------

## Notes

Note Derating:	Notice derating
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.
Note:	Do not connect or disconnect under load.

## Variants

Item #	Item Description	Cable Length
935034001	RSMWVS-4D-0467/01 M	1 m
935034002	RSMWVS-4D-0467/02 M	2 m
935034003	RSMWVS-4D-0467/05 M	5 m
935034004	RSMWVS-4D-0467/10 M	10 m

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.