



Product: [RSRK 1201M-654](#) 

MINI 1-1/8" | Cordset | Male Straight → Female Straight, 12-pin, PUR (0.75 mm²) 18 AWG, 300 V / 5 A

Product Description

MINI 1-1/8" | Double-Ended Cordset | 1-1/8" Male Straight, #Contacts 10 → 1-1/8" Male Straight, #Contacts 12, Cable: Yellow PUR; 0.75 mm² (18 AWG), 300 V / 7 A

Technical Specifications

Face View Side 1

Pin 1	Pin 2	Pin 3	Pin 4	Pin 5	Pin 6	Pin 7	Pin 8	Pin 9	Pin 10	Pin 11	Pin 12
orange	blue	white/black	red/black	green/black	orange/black	blue/black	black/white	green	red	white	black

Face View Side 2

Pin 1	Pin 2	Pin 3	Pin 4	Pin 5	Pin 6	Pin 7	Pin 8	Pin 9	Pin 10	Pin 11	Pin 12
orange	blue	white/black	red/black	green/black	orange/black	blue/black	black/white	green	red	white	black

Product Description

Product Family:	Power Connector
Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Shielding Type:	Unshielded
Rated Voltage (UL):	300 V
Operating Voltage:	300 V AC/DC
Current Rating:	5 A

Technical Data Side 1

Side 1 Product Sub Family:	MINI 1-1/8"
Side 1 Type of Contact/Gender:	Pin Contact / Male
Connector Design:	Molded 1-1/8" Male Straight
Attachment Type:	Coupling Nut Female Thread
Number of Pins:	12 (11+PE)
Coding, Side 1:	A
Side 1 Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10 ⁹ Ohm
Ambient Temperature (Operation)*:	- 40° C to + 80° C
Protection Degree / IP Rating**:	IP67
Side 1 Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	III acc. to IEC 60664-1
Contact Base Material:	Copper Alloy (CuZn)
Side 1 Contact Plating:	Copper-Silver-Gold-Alloy (Cu/Ag/Au)
Contact Bearer Material:	Thermoplastic polyurethane (TPU)
Contact Bearer Color:	Yellow
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	Thermoplastic polyurethane (TPU)
Molded Body Color:	Yellow

Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	Aluminum (Al)
Attachment Plating:	Anodized Black
Fastening Torque (Attachment):	MINI: 70 Ncm, hand-tight
Note:	1. Do not connect or disconnect under load.

Cable Data

Cable Number:	654
Conductor Size:	18 AWG
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 5 mio
Conductor Material:	Cu
Cable Jacket Material:	Polyurethane (PUR)
Cable Jacket Color:	Yellow
Cable Diameter D:	Ø 8.99 mm 0.354"
Wire Insulation Material:	Polyvinyl Chloride (PVC)
Insulated Wire Diameter:	Ø 1.73 mm 0.068"
Overall Shield (Cable):	Unshielded
Ambient Temperature (Fixed Installation):	- 40° C to + 80° C
Ambient Temperature (Flex Installation):	- 5° C to + 80° C
Ambient Temperature (Fixed Installation short-term 100h):	- 40° C to + 80° C
Ambient Temperature (Drag Chain Inst):	- 5° C to + 80° C
UL Cable Type:	AWM Style 20233
Flammability Class (Cable Jacket):	FT1, VW-1

Technical Data Side 2

Side 2 Product Sub Family:	MINI 1-1/8"
Side 2 Type of Contact/Gender:	Socket Contact / Female
Connector Design, Side 2:	Molded 1-1/8" Female Straight
Attachment Type, Side 2:	Coupling Nut Female Thread
Number of Pins, Side 2:	12 (11+PE)
Coding, Side 2:	A
Contact Resistance, Side 2:	≤ 10 mOhm
Ambient Temperature (Operation), Side 2*:	- 40° C to + 80° C
Overvoltage Category, Side 2:	III acc. to IEC 60664-1
Contact Base Material, Side 2:	Copper Alloy (CuZn)
Contact Bearer Material, Side 2:	Thermoplastic polyurethane (TPU)
Contact Bearer Color, Side 2:	Yellow
Flammability Class (Contact Bearer), Side 2:	UL 94 HB
Molded Body Material, Side 2:	Thermoplastic polyurethane (TPU)
Molded Body Color, Side 2:	Yellow
Flammability Class (Molded Body), Side 2:	UL 94 HB
Attachment Material, Side 2:	Aluminum (Al)
Attachment Plating, Side 2:	Anodized Black
Fastening Torque (Attachment), Side 2:	MINI: 70 Ncm, hand-tight
Note, Side 2:	1. Do not connect or disconnect under load.

Approvals

UL-File:	E315587
UL:	UL 2238; cURus

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Resistances

Halogenfree:	Yes
--------------	-----

Oil Resistance:	Yes
-----------------	-----

Notes

Protection Degree / IP Rating Note:	IP Rating tested according to IEC standard using combination of a Hirschmann or Lumberg Automation connector mounted and locked
Note Derating:	* Notice derating

Variants

Item #	Item Description	Cable Length
500001852	RSRK 1201M-654/6F	6 ft
500001855	RSRK 1201M-654/12F	12 ft
500001856	RSRK 1201M-654/15F	15 ft
500001857	RSRK 1201M-654/20F	20 ft
500001859	RSRK 1201M-654/30F	30 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.