




**Product:** [RSRK 30-731](#)

7/8" Power Double-Ended Cordset: Male straight to female straight, 3-pin, yellow body, 300 V (UL), 8 A (UL); TPE yellow cable, 18 AWG

**Product Description**

7/8" Power Double-Ended Cordset: Male straight to female straight, 3-pin, yellow body, 300 V (UL), 8 A (UL); TPE yellow cable, 18 AWG

**Technical Drawing**



**Technical Specifications**

**Product Description**

Product Family:	Power Connector
Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Shielding:	Unshielded
Rated Voltage (UL):	300 V
Rated Current (UL)*:	8 A

**Technical Data Side 1**

Product Sub Family:	7/8"
Type of Contact / Gender:	male
Connector Design:	straight
Attachment Type:	Coupling nut with external threads
Number of Pins:	3
Ambient Temperature (Operation)*:	-40°C to +90°C
Protection Degree / IP Rating**:	IP 67 / NEMA 6P
Contact Base Material:	CuZn
Contact Plating:	gold over silver plated
Contact Bearer Material:	TPU
Contact Bearer Color:	yellow
Molded Body Material:	TPU
Molded Body Color:	yellow

**Cable Data**

Cable Number:	731
Conductor Size:	18 AWG
Number of Wires:	3
Cable Jacket Material:	TPE
Cable Jacket Color:	Yellow

Cable Diameter D:	.284" (7.2 mm)
UL Cable Type:	PLTC

## Technical Data Side 2

Product Sub Family, Side 2:	7/8" Circular Connectors
Type of Contact / Gender, Side 2:	female
Connector Design, Side 2:	straight
Attachment Type, Side 2:	Coupling nut with internal threads
Number of Pins, Side 2:	3
Ambient Temperature (Operation), Side 2*:	-40°C to +90°C
Protection Degree / IP Rating, Side 2**:	* only if mounted and locked in combination with Hirschmann / Lumberg connector.
Contact Base Material, Side 2:	CuZn
Contact Plating, Side 2:	gold over silver plated
Contact Bearer Material, Side 2:	TPU
Contact Bearer Color, Side 2:	yellow
Molded Body Material, Side 2:	TPU
Molded Body Color, Side 2:	yellow

## Approvals

UL:	UL 2238 Recognized
-----	--------------------

## Safety & Environmental Compliance

RoHS Compliant:	yes
-----------------	-----

## Notes

Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.
-------------------------------------	--

## History

Update and Revision:	Revision Number: 0.65 Revision Date: 03-22-2023
----------------------	---

## Variants

Item #	Item Description	Cable Length
500004255	RSRK 30-731/0.5M	0.5 m
500004256	RSRK 30-731/1M	1 m
500004257	RSRK 30-731/3M	3 m
500002770	RSRK 30-731/6F	6 ft
500004258	RSRK 30-731/7M	7 m
500004259	RSRK 30-731/9M	9 m
500002771	RSRK 30-731/12F	12 ft
500004260	RSRK 30-731/15M	15 m
500002800	RSRK 30-731/15F	15 ft
500004261	RSRK 30-731/20M	20 m
500002772	RSRK 30-731/20F	20 ft
500004262	RSRK 30-731/25M	25 m
500002773	RSRK 30-731/30F	30 ft

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.