



Product: [RST 4-RKT 4-633](#) 

M12 Micro actuator/sensor cordset, double-ended, 4-poles, male straight to female straight connector with self-locking thread and yellow PVC 22 gauge molded cable, IEC color code.

Product Description

M12 Micro actuator/sensor cordset, double-ended, 4-poles, male straight to female straight connector with self-locking thread and yellow PVC 22 gauge molded cable, IEC color code.

Technical Specifications

Product Description

Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Voltage Rating:	5 pole: 60 V, 8 pole: 30 V AC / 36 V DC

Technical Data Side 1

Connector Design:	Straight 0°
Attachment Type:	Coupling Screw
Number of Pins:	4
Coding, Side 1:	A
Side 1 Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10 ⁹ Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	-40°C (-40°F) / +90°C (194°F)
Side 1 Design Standard:	IEC 61076-2-101
Side 1 Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	II acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material:	CuSn
Contact Bearer Material:	TPU
Contact Bearer Color:	Yellow
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	TPU
Molded Body Color:	Yellow
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	CuZn
Attachment Plating:	Nickel-plated
O-Ring Material:	FKM
Fastening Torque (Attachment):	M 12x1: (50-60) Ncm, hand-tight

Cable Data

Cable Number:	633
Conductor Size:	22 AWG
Conductor Material:	Cu
Cable Jacket Material:	PVC
Cable Jacket Color:	Yellow
Cable Diameter D:	.190" (4.8 mm)

Ambient Temperature (Fixed Installation):	-40°C (-40°F) / +90°C (194°F)
Cable Characteristics:	Free of lacquer wetting disturbing substances; Exclusion of silicone

Technical Data Side 2

Connector Design, Side 2:	Straight 0°
Attachment Type, Side 2:	Coupling Screw
Coding, Side 2:	A
Contact Resistance, Side 2:	≤ 10 mOhm
Pollution Degree, Side 2:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material, Side 2:	CuSn
Contact Plating, Side 2:	Cu/Au
Contact Bearer Material, Side 2:	TPU
Contact Bearer Color, Side 2:	Black
Flammability Class (Contact Bearer), Side 2:	UL 94 HB
Molded Body Material, Side 2:	TPU
Molded Body Color, Side 2:	Yellow
Flammability Class (Molded Body), Side 2:	UL 94 HB
Attachment Material, Side 2:	CuZn
Attachment Plating, Side 2:	Nickel-plated

Approvals

UL-File:	E315587
UL:	UL 2238; cURus

Notes

Note Derating:	Notice derating
----------------	-----------------

Variants

Item #	Item Description
600000806	RST 4-RKT 4-633/0.3M
600000807	RST 4-RKT 4-633/0.6M
600000808	RST 4-RKT 4-633/1.5M
600000809	RST 4-RKT 4-633/10M
600000811	RST 4-RKT 4-633/1M
600000812	RST 4-RKT 4-633/25M
600000814	RST 4-RKT 4-633/2M
600000815	RST 4-RKT 4-633/5M
600002919	RST 4-RKT 4-633/4M
600003854	RST 4-RKT 4-633/3M
600003861	RST 4-RKT 4-633/12M
600003862	RST 4-RKT 4-633/8M
600003884	RST 4-RKT 4-633/7M
600004263	RST 4-RKT 4-633/20M
600006187	RST 4-RKT 4-633/30M
600003856	RST 4-RKT 4-633/15M
600006570	RST 4-RKT 4-633/7.5M
600006686	RST 4-RKT 4-633/14M
600006688	RST 4-RKT 4-633/3.5M
600006707	RST 4-RKT 4-633/26M

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.