



Product: [RKWT 8-627](#) 

M12 Micro Actuator/sensor cordset, single-ended, 8-poles, female right-angle connector with self-locking thread and black 24 gauge PVC molded cable."

Product Description

M12 Micro Actuator/sensor cordset, single-ended, 8-poles, female right-angle connector with self-locking thread and black 24 gauge PVC molded cable."

Technical Specifications

Technical Data

Side 1 Product Sub Family:	M12 Standard
Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Side 1 Type of Contact/Gender:	Female
Connector Design:	Angled
Number of Pins:	8
Coding, Side 1:	A
Attachment Type:	Coupling Screw
Voltage Rating:	33 V
Rated Impulse Voltage:	0.8 kV
Operating Voltage:	33 V AC/DC
Side 1 Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10 ⁹ Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 40 °C - + 90 °C
Protection Degree / IP Rating**:	IP67
Side 1 Design Standard:	IEC 61076-2-101
Side 1 Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)

Materials

Contact Base Material:	CuZn
Side 1 Contact Plating:	Cu/Au
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	TPU
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	CuZn
Attachment Plating:	Nickel-plated
O-Ring Material:	FKM or Viton

Additional Technical Data

Fastening Torque (Attachment):	M 12x1: (50-60) Ncm, hand-tight
--------------------------------	---------------------------------

Cable Data

Cable Number:	627
Conductor Size:	24 AWG
Number of Wires:	8
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 1 M
Conductor Material:	Cu
Cable Jacket Material:	PUR
Cable Jacket Color:	Gray
Cable Diameter D:	0.237"
Wire Insulation Material:	PVC
Insulated Wire Diameter:	.043"
UL Cable Type:	AWM 2661
Flammability Class (Cable Jacket):	FT-1
Cable Characteristics:	Good chemical and oil resistance

Safety & Environmental Compliance

RoHS Compliant:	yes
-----------------	-----

Resistances

Halogenfree:	DIN EN 50267-2-1, IEC 60754-1, VDE 0482-267-2-4
--------------	---

Notes

Note Derating:	Notice derating
----------------	-----------------

History

Update and Revision:	Revision Number: 0.30 Revision Date: 05-26-2026
----------------------	---

Variants

Item #	Item Description
600001991	RKWT 8-627/2M
600001992	RKWT 8-627/5M
600001993	RKWT 8-627/10M
600006232	RKWT 8-627/15M

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.