



Product: [RSWT 5-3-GAN22LU-D24-241](#)


M12-Form A | M12- Male 90° | #Contacts: 3 | Form A - Female 90° | #Contacts: 2+2 PE | Recovery Diode (FRD) & yellow LED | 24 V | Cable: Orange (PUR); 0.50 mm²; IEC | cURus

Product Description

M12 - Form A, Double-Ended Cordset| M12- Male Angled | #Contacts: 3, A-coded | Form A - Female Angled Cordset | #Contacts: 2+2 PE | Recovery Diode (FRD) & yellow LED | 24 V / 4 A | Cable: Orange PUR Jacket; 3x0.50 mm² (20 AWG); IEC | UL 2238; cURus

Technical Drawing

D2 - Fast Recovery Diode (FRD) and LED



Technical Specifications

Face View Side 1

Pin 3	Pin 4	Pin 5
blue	brown	green-yellow

Face View Side 2

Pin 1	Pin 2	PE1	PE2
brown	blue	green-yellow	green-yellow

Product Description

Product Family:	Valve Connectors
-----------------	------------------

Brand:	Hirschmann
Connector Type:	Cordset, double ended
Shielding:	Unshielded
Replacement for:	RSWT 5-3-VAD 1F-4-3-241
Rated Voltage:	24 V
Rated Impulse Voltage:	4.0 kV (PCBA 2.0 kV)
Operating Voltage:	24 V DC
Rated Current*:	4 A

Technical Data Side 1

Product Sub Family:	RSWT - M12 Standard
Type of Contact / Gender:	Pin Contact / Male
Connector Design:	Angled (90°) Body
Attachment Type:	Coupling Screw
Number of Pins:	3
Coding:	A
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10^9 Ohm
Mating Cycles:	≤ 100
Conductor Cross Section:	0.50 mm²
Ambient Temperature (Operation)*:	- 40 °C - + 90 °C
Protection Degree / IP Rating*:	IP65, IP67, IP68 (1 m / 24 h), IP69K
Design Standard:	IEC 61076-2-101
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Clearance / Creepage Distance:	DIN EN 60664-1 (2008/01); VDE 0110-1
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material:	Copper Alloy (CuSn)
Contact Plating:	Gold over Copper (Cu/Au)
Contact Bearer Material:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color:	Orange
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	Thermoplastic Polyurethane (TPU)
Molded Body Color:	Grey Translucent
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	Brass (CuZn)
Attachment Plating:	Nickel (Ni)
Fastening Torque (Attachment):	M 12x1: (50-60) Ncm, hand-tight

Cable Data

Cable Number:	241
Conductor Size:	0.5 mm²
Number of Wires:	3
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 5 mio
Conductor material:	Cu
Cable Jacket Material:	Polyurethane (PUR)
Cable Jacket Color:	Orange
Cable Diameter D:	Ø 3.25 mm [0.128 "]
Wire Insulation Material:	High-density polyethylene (HDPE)
Insulated Wire Diameter:	Ø 1.50 mm [0.06 "]
Ambient Temperature (Fixed Installation):	- 40 °C to + 90 °C (UL: + 80 °C)

Ambient Temperature (Flex Installation):	- 20 °C to + 90 °C (UL: + 80 °C)
Ambient Temperature (Drag Chain Inst):	- 25 °C to + 60 °C
UL Cable Type:	AWM: 20549
Flammability Class (Cable Jacket):	DIN EN 50265-2-2, VDE 0482-265-2-2, IEC 60332-2-2, CSA FT2
Cable Characteristics:	Flexibility: Excellent Abrasion Resistance: Excellent Oil & Chemical Resistance: Excellent UV Resistance: Good to excellent Low Temp Performance: Excellent (flexible to -40°C) Flame Retardance: Varies Halogen-Free: Yes Mechanical Durability: High (resists impact, tear, and flex) Environmental Suitability: Outdoor, oily, wet, or rough environments

Technical Data Side 2

Product Sub Family, Side 2:	GAN - cURus 2238
Type of Contact / Gender, Side 2:	Socket Contact / Female
Connector Design, Side 2:	Angled (90°) Body
Attachment Type, Side 2:	Central Screw
Number of Pins, Side 2:	2+2 PE
Coding, Side 2:	A
Contact Resistance, Side 2:	≤ 10 mOhm
Insulation Resistance, Side 2:	> 10^9 Ohm
Mating Cycles, Side 2:	≤ 50
Ambient Temperature (Operation), Side 2*:	- 25 °C - + 85 °C [Extended Temperature - 40 °C - + 105 °C with additional gasket accessory, 934887001]
Protection Degree / IP Rating, Side 2**:	IP65, IP67 (IP69K: without additional gasket; max. +80 °C)
Design Standard, Side 2:	DIN EN 175301-803-A, ISO 4400
Pollution Degree, Side 2:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Clearance / Creepage Distance, Side 2:	DIN EN 60664-1 (2008/01); VDE 0110-1
Overvoltage Category, Side 2:	III acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material, Side 2:	Brass (CuZn)
Contact Plating, Side 2:	Copper over Tin (Cu/Sn)
Contact Bearer Material, Side 2:	Glass-filled Polyamides (PA GF)
Contact Bearer Color, Side 2:	Black
Flammability Class (Contact Bearer), Side 2:	UL 94 V-0
Molded Body Material, Side 2:	Thermoplastic Polyurethane (TPU)
Molded Body Color, Side 2:	Grey Translucent
Flammability Class (Molded Body), Side 2:	UL 94 HB
Attachment Material, Side 2:	Steel, Philips combi slot
Gasket Material, Side 2:	Molded Integrated Gasket
Function Indicator, Side 2:	Yellow LED
Protective Circuit, Side 2:	Recovery Diode (FRD)
Fastening Torque (Attachment), Side 2:	(50-60) Ncm
Accessories to Order Separately, Side 2:	934887001 - GAN EPDM gasket and holding clip
Note, Side 2:	1. Do not connect or disconnect under load. 2. Extended temperature range of -40°C performed by Belden in mated condition using EPDM gasket accessory.

Approvals

UL-File:	E315587
UL:	UL 2238; cURus
VDE:	Yes

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Resistances

Halogenfree:	Yes
Oil Resistance:	Good chemical and oil resistance

Notes

Note Derating:	Notice derating
Update and Revision:	Revision Number: 0.4 Revision Date: 07-04-2025

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.