



**Product:** [RV6FFPSBK18-S1](#)

REVConnect Shielded FlexPlug, CAT6+, 4 Pair, 23 AWG Solid, CMP, T568A/B-T568A/B

### Product Description

REVConnect Shielded FlexPlug, CAT6+, Single Packaging (incl. 1 core), 4 Pair, 23 AWG Solid, Black, CMP, T568A/B-T568A/B

### Technical Specifications

#### Product Overview

Suitable Applications:	IBDN System 4800, IBDN System 3600, IBDN System 2400, TIA Category 6, ISO Class E, 1000BASE-T, Surveillance, PoE++, PoE+, PoE, Noisy Environments
------------------------	---

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	No. of Pairs
23	Solid	4

#### Connectors

##### Materials

Type
RJ45
RJ45 Blades
REVConnect

#### Electrical Characteristics

Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum

#### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

#### Mechanical Characteristics

Tool Compatibility:	RVUTT01 Termination Tool
Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	750 cycles
Termination Rear Connection:	Mated Connection
Termination Rear Connection Durability:	200 cycles

##### Termination Interface

Termination	Durabilities
Cable End 1 - RJ45	750 Cycles
Cable End 2 - RevConnect	200 Cycles

#### Standards

UL Rating:	UL94 V-0, UL1863, UL2043
------------	--------------------------

Data Category:	Category 6
TIA/EIA Compliance:	Category 6 - TIA 568.C.2, ISO/IEC 11801:2002 Ed.2
IEEE Compliance:	Power Over Ethernet (PoE) IEEE 802.3at type 1 and 2 (up to 30W), IEEE802.3bt/D1.7 type 3 and 4 (up to 100W), CISCO UPOE (up to 60W), Power over HDBaseTTM (up to 100W)

## Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL2043 Air Handling Spaces
Safety Listing:	c(UL)us Listed

## Related Part Numbers

Related Parts:	REVConnect
----------------	------------

## History

Update and Revision:	Revision Number: 0.11 Revision Date: 04-08-2022
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.