





Product: [RSRK 801M-898](#)

1" Power Double-Ended Cordset: Male to Female, 8-pin, 600 V, 7 A; TPE yellow cable, 16 AWG


Product Description

1" Power Double-Ended Cordset: Male, straight, 8-pin to Female, straight, 8-pin, yellow body, 600 V, 7 A; TPE yellow cable, 16 AWG, TC-ER Rated, US Color Code

Technical Drawing



1 = OR
2 = BU
3 = WH/BK
4 = BK
5 = WH
6 = RD
7 = GN
8 = RD/BK
US COLOR CODE



1 = OR
2 = BU
3 = WH/BK
4 = BK
5 = WH
6 = RD
7 = GN
8 = RD/BK
US COLOR CODE

Technical Specifications

Product Description

Product Family:	Power Connector
Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Shielding:	Unshielded
Rated Voltage:	600 V
Rated Current*:	7 A

Technical Data Side 1

Product Sub Family:	1"
Type of Contact / Gender:	Male
Connector Design:	Straight
Attachment Type:	Coupling nut with internal threads
Number of Pins:	8
Ambient Temperature (Operation)*:	-40 °C to +90 °C
Protection Degree / IP Rating**:	IP65, IP67

Contact Base Material:	CuZn
Contact Plating:	Au over Ag
Contact Bearer Material:	TPU
Contact Bearer Color:	YE
Molded Body Material:	TPU
Molded Body Color:	yellow
Attachment Material:	Anodized Bk, Al

Cable Data

Cable Number:	898
Conductor Size:	16 AWG (65/34)
Number of Wires:	8
Minimal Bending Radius (Flexible Inst):	> 10 x D
Conductor material:	Stranded, BC
Cable Jacket Material:	TPE
Cable Jacket Color:	Yellow
Cable Diameter D:	Ø 10.92 mm
Wire Insulation Material:	PVC-Nylon
Insulated Wire Diameter:	Ø 2.77 mm
Ambient Temperature (Fixed Installation):	-30C TO 90C DRY, 75C WET
UL Cable Type:	NEC TYPE TC-ER (UL1277)
Flammability Class (Cable Jacket):	UL 1685, CSA FT4, IEEE 1202
Cable Characteristics:	Oil and Coolant, Vibration, UV, Abrasion, and Weld Spark resistant, Continuous Flex

Technical Data Side 2

Product Sub Family, Side 2:	1"
Type of Contact / Gender, Side 2:	Female
Connector Design, Side 2:	Straight
Attachment Type, Side 2:	Coupling nut with internal threads
Number of Pins, Side 2:	8
Ambient Temperature (Operation), Side 2*:	-40 °C to +90 °C
Protection Degree / IP Rating, Side 2**:	IP65, IP67
Contact Base Material, Side 2:	CuZn
Contact Plating, Side 2:	Au over Ag
Contact Bearer Material, Side 2:	TPU
Contact Bearer Color, Side 2:	YE
Molded Body Material, Side 2:	TPU
Molded Body Color, Side 2:	yellow
Attachment Material, Side 2:	Anodized Bk, Al
Note, Side 2:	Do not connect / disconnect under load.

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Protection Degree / IP Rating Note:	Protection Degree and IP Rating per test standard IEC 60529 using a Lumberg Automation mating product
Note Derating:	Notice Derating

Variants

Item #	Item Description	Cable Length	Replacement for
500004640	RSRK 801M-898/1M	1 m	RSRK 801M-698
500004612	RSRK 801M-898/2M	2 m	RSRK 801M-698
500004641	RSRK 801M-898/3M	3 m	RSRK 801M-698
500004616	RSRK 801M-898/4M	4 m	RSRK 801M-698
540001747	RSRK 801M-898/5M	5 m	RSRK 801M-698
540001748	RSRK 801M-898/6M	6 m	RSRK 801M-698
540001750	RSRK 801M-898/10M	10 m	RSRK 801M-698
540004082	RSRK 801M-898/21.5M	21.5 m	RSRK 801M-698
540004584	RSRK 801M-898/18.5M	18.5 m	RSRK 801M-698

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.