

Product: [RVUTA21](#) 

REVConnect FlexPlug Test Adapter Kit



Product Description

REVConnect FlexPlug Test Adapter Kit

Technical Specifications

Product Overview

Suitable Applications:	REVConnect system testing. For use in permanent link testing.
------------------------	---

Physical Characteristics (Overall)

Wiring Scheme:	T568A/B
Packaging:	Individually packaged in a clear plastic bag.

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-20°C To +60°C

Mechanical Characteristics

Plug /Jack Compatibility:	RJ45, REVConnect Core
---------------------------	-----------------------

Termination Interface

Termination	Connection	Durabilities
Cable End 1 - RJ45	Mated Connection	1000 Cycles
Cable End 2 - REVConnect	Mated Connection	1000 Cycles
RJ45	Mated Connection	

Standards

TIA/EIA Compliance:	Category 6A - ANSI/TIA 568.2-D, Category 6A - ISO/IEC 11801-1
---------------------	---

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Part Number

Related Parts:	RVUTA01, RVUTA22, RVUTA02
----------------	---------------------------

Product Notes

Included Parts:	RVUTA22, AX104552
-----------------	-------------------

History

Update and Revision:	Revision Number: 0.9 Revision Date: 03-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.