



Product: [Rail Power Injector, RPI-P1-8PoE](#) 

Industrial, fanless Fast/Gigabit PoE Injector, PoE/PoE+ (IEEE 802.3at), 30W (25.5W at load) per port

Product Description

The RPI-P1-8PoE is a DIN-rail mountable DC-only input PoE injector with built-in PoE+ functionality. It provides 8x RJ45 Ethernet ports for data input and 8xRJ45 Ethernet ports with PoE+ according to standard IEEE802.3at.

Technical Specifications

Product description

Type:	RPI-P1-8PoE
Part Number:	942225001
Port type and quantity:	8 x 10/100/1000 BASE-TX ports

Power requirements

Operating Voltage:	48 - 56 VDC
Power consumption:	245 W

Ambient conditions

MTBF:	152 years (48V/5.4A) (according SN29500, IEC61709)
Operating temperature:	-25-+70 °C
Relative humidity (non-condensing):	5-95 %

Mechanical construction

Dimensions (WxHxD):	39 mm x 128 mm x 117 m
Weight:	360 g
Protection class:	IP20

Approvals

Safety of industrial control equipment:	EN60950-1, EN 61131-2 , cUL60950-1 (pending)
Transportation:	EN50121-4

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com
Certificates:	https://www.doc.hirschmann.com/certificates.html

Variants

Item #	Type
942225001	RPI-P1-8PoE

Update and Revision:	Revision Number: 0.66 Revision Date: 12-15-2021
----------------------	-------------------------------------------------

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.