



Product: [SCSH2216LLF](#)

FX UHD Splitter Cassette OS2, 2x16



Product Description

FX UHD Splitter Cassette, OS2, 2x16, 2 Splitters, LC/APC Input, LC/APC Output, Front

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Construction

Fiber Cable Construction

Fiber Type	
OS2, G.657.A1, G.652.D	
Weight:	0.5 lbs
Overall Height:	1.5 in
Overall Width:	4.5 in
Overall Length:	6.9 in

Physical Specifications

Max Capacity:	16 Fibers (Output)
---------------	--------------------

Optical Characteristics

Wavelength:	1260-1650 NANOMETERS
-------------	----------------------

Mechanical Characteristics

Front Connection:	Static
Termination Style:	Front

Temperature Range

Operating Temperature Range:	-40°C To +85°C
Storage Temperature Range:	-40°C To +85°C

Product Material

Materials

Description	Material	Color	Type
Housing	PC/ABS	Black	
Cover	Polycarbonate	Black	
Frame	PC/ABS	Black	Lead Frame
Adapter Output	Plastic - UL94V-0	Green	LC-Quad w/ Internal Shutters
Adapter Input	Plastic - UL94V-0	Green	LC-Quad w/ Internal Shutters

Transmission-Characteristics

Transmission Specifications

Splitter Configuration	IL Max (dB)	Uniformity Max (dB)	PDL Max (dB)	Directivity Min (dB)	RL Min (dB)
2 x 16	14.8	1.8	0.4	-55	-55

Standards

TIA/EIA Compliance:	Telcordia GR-1209-CORE (splitters only), Telcordia GR-1221-CORE (splitters only)
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Related Parts:	FX UHD & FXU Patch Panels, FX Patch Cords
----------------	---

Product Notes

Packaging:	Individually packaged in a plastic shell. Shipped in cardboard box (14/box)
------------	---

History

Update and Revision:	Revision Number: 0.253 Revision Date: 10-07-2025
----------------------	--

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.