



Product: [TE-1LD-288-RX2N](#) 

Mining Grade Indoor/Outdoor Multi-Loose-Tube OM1 288 Fibers Dry Tubes 2.5mm Rodent Resistant Double Jacket CPE/PVC OFNR-ST1 Oil Res.1&2 MSHA

Product Description

Mining Grade, Indoor/Outdoor, Multi-Loose-Tube, OM1, 288 Fibers, Dry Tubes 2.5mm, Rodent Resistant, Double Jacket, Black, CPE/PVC, OFNR-ST1, Oil Res 1 & 2, MSHA Approved

Technical Specifications

Product Overview

Product Category:	Fiber Multi-Loose Tube Cable
Suitable Applications:	Mining, Harsh Environment, IoT, Factory or Process Automation, IP Cameras And Devices, Data Communication

Fiber Specifications

Fiber Type:	OM1
Fiber Core Diameter:	62.5/125 µm
Fiber Diameter:	250 µm
Fiber Count:	288
Fiber Color Coding:	TIA-598-D

Cable Construction

Number of Active Subunits:	24
Fibers Per Subunit:	12
Subunit Waterblocking:	Gel Free
Subunit Diameter:	0.098 in (2.5 mm)
Central Strength Member Type:	GRP

Inner Jacket Specifications

Material:	CPE - Chlorinated Polyethylene
Nominal Diameter@InnerJacket1 (cnv):	0.681 in (17.3 mm)
Color:	Black
Number of Inner Jacket Ripcords:	1

Outer Jacket Specifications

Strength Member:	Fiberglass Yarns
Jacket Material:	CPE - Chlorinated Polyethylene
Nom. Diameter:	0.849 in (21.5 mm)
Outer Jacket Color:	Black
Outer Jacket Ripcord:	1

Optical Characteristics

Wavelength	850 nm	1300 nm
Max. Attenuation	3.5 dB/km	1.25 dB/km
10 Gigabit Ethernet Performance	33 m	--
Min. Overfilled Launch (OFL) Bandwidth	200 MHz.km	500 MHz.km

Mechanical Characteristics

Minimum Bend Radius During Installation:	15x Cable OD
Minimum Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	4448 N (1000lbf)
Max. Tensile Strength During Operation:	1320 N (300lbf)
Crush Resistance:	440 N/cm
Bulk Cable Weight:	212 lbs/kft (315 kg/km)

Temperature Range

Installation Temperature Range:	-30°C to +60°C
Operating Temperature Range:	-50°C to +85°C
Storage Temperature Range:	-50°C to +85°C

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL1666, UL 1685
NEC / UL Compliance:	OFNR-ST1
CEC / C(UL) Compliance:	OFNG-ST1
ICEA Compliance:	S-104-696
TIA/EIA Compliance:	568.3, 598-D
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment)

Product Notes

Notes:	Ozone Resistance, PMSHA - 07-KA250002-MSHA
--------	--

History

Update and Revision:	Revision Number: 0.2 Revision Date: 05-28-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type
TE-1LD-288-RX2N	Black	Reel

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.