





Product: [RST 5-RKT 5-794](#) 

M12 - Male 0° to Female 0° | #Contacts: 5 | 30 V | Cable TPE YE, 18 AWG, IEC | cURus

Product Description

M12 - Molded Cordset Male Straight to Female Straight | #Contacts: 5 | 30 V / 4 A | Cable TPE Yellow, 5x18 AWG, IEC | cURus 2238

Technical Drawing



Technical Specifications

Product Description

Product Family:	Sensor / Actuator Connectors
Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Shielding:	Unshielded
Rated Voltage:	30 V
Rated Impulse Voltage:	2.5 kV
Rated Current*:	4 A

Product Sub Family:	M12 Standard
Type of Contact / Gender:	Pin Contact / Male
Connector Design:	Straight (0°) Body
Attachment Type:	Coupling Screw
Number of Pins:	5
Coding:	A
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10^9 Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 40 °C - + 90 °C
Protection Degree / IP Rating**:	IP65, IP67
Design Standard:	IEC 61076-2-101
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	II acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material:	Copper-Tin (CuSn)
Contact Plating:	Copper over Gold (Cu/Au)
Contact Bearer Material:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color:	Yellow
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	Polyurethane (PUR)
Molded Body Color:	Yellow
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	Brass (Cu/Zn)
Attachment Plating:	Nickel-plated (Ni)
Fastening Torque (Attachment):	M 12x1: (50-60) Ncm, hand-tight

Cable Data

Cable Number:	794
Conductor Size:	18 AWG
Number of Wires:	5
Minimal Bending Radius (Fixed Inst):	> 7 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 5 M
Conductor material:	Cu
Cable Jacket Material:	Thermoplastic Elastomer (TPE)
Cable Jacket Color:	Yellow
Cable Diameter D:	Ø 7.70 mm [0.304"]
Wire Insulation Material:	Polyvinyl Chloride (PVC)
Insulated Wire Diameter:	Ø 2.03 mm [0.080"]
Ambient Temperature (Fixed Installation):	- 35 °C - + 105 °C
Ambient Temperature (Flex Installation):	+ 5 °C - + 105 °C
UL Cable Type:	PLTC
Flammability Class (Cable Jacket):	CSA FT-4
Cable Characteristics:	Oil Resistant, C-Track rated

Technical Data Side 2

Product Sub Family, Side 2:	M12 Standard
Type of Contact / Gender, Side 2:	Socket Contact / Female
Connector Design, Side 2:	Straight (0°) Body
Attachment Type, Side 2:	Coupling Nut
Number of Pins, Side 2:	5
Coding, Side 2:	A
Contact Resistance, Side 2:	≤ 10 mOhm
Insulation Resistance, Side 2:	> 10^9 Ohm
Mating Cycles, Side 2:	≤ 100
Ambient Temperature (Operation), Side 2*:	- 40 °C - + 90 °C
Operating Temperature (UL), Side 2:	max. + 50 °C

Protection Degree / IP Rating, Side 2**:	IP65, IP67
Design Standard, Side 2:	IEC 61076-2-101
Pollution Degree, Side 2:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category, Side 2:	II acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material, Side 2:	Copper-Tin (CuSn)
Contact Plating, Side 2:	Copper over Gold (Cu/Au)
Contact Bearer Material, Side 2:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color, Side 2:	Yellow
Flammability Class (Contact Bearer), Side 2:	UL 94 HB
Molded Body Material, Side 2:	Thermoplastic Polyurethane (TPU)
Molded Body Color, Side 2:	Yellow
Flammability Class (Molded Body), Side 2:	UL 94 HB
Attachment Material, Side 2:	Brass (Cu/Zn)
Attachment Plating, Side 2:	Nickel-plated (Ni)
O-Ring Material, Side 2:	FKM, green
Fastening Torque (Attachment), Side 2:	M 12x1: (50-60) Ncm, hand-tight

Approvals

UL-File:	E104696
UL:	UL 2238; cURus

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Variants

Item #	Item Description	Cable Length
600005527	RST 5-RKT 5-794/0.5M	0.5 m
600005528	RST 5-RKT 5-794/1M	1 m
600005529	RST 5-RKT 5-794/1.5M	1.5 m
600005530	RST 5-RKT 5-794/2M	2 m
600005531	RST 5-RKT 5-794/3M	3 m
600005532	RST 5-RKT 5-794/5M	5 m
600005533	RST 5-RKT 5-794/7M	7 m
600005534	RST 5-RKT 5-794/10M	10 m
600005535	RST 5-RKT 5-794/15M	15 m
600005536	RST 5-RKT 5-794/20M	20 m
600005612	RST 5-RKT 5-794/4M	4 m
600005613	RST 5-RKT 5-794/12M	12 m
600005614	RST 5-RKT 5-794/25M	25 m
600005643	RST 5-RKT 5-794/6M	6 m
600005988	RST 5-RKT 5-794/0.6M	0.6 m
600006008	RST 5-RKT 5-794/30M	30 m
600006069	RST 5-RKT 5-794/50M	50 m
600006229	RST 5-RKT 5-794/8M	8 m
600006462	RST 5-RKT 5-794/0.3M	0.3 m
600006550	RST 5-RKT 5-794/18M	18 m
600006730	RST 5-RKT 5-794/40M	40 m
600006731	RST 5-RKT 5-794/45M	45 m
600006732	RST 5-RKT 5-794/55M	55 m
600006833	RST 5-RKT 5-794/65M	65 m
600006834	RST 5-RKT 5-794/85M	85 m
600006835	RST 5-RKT 5-794/100M	100 m
600006947	RST 5-RKT 5-794/35M	35 m
600007323	RST 5-RKT 5-794/75M	75 m
600007336	RST 5-RKT 5-794/60M	60 m

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.