



**Product:** [TT-SAG-012-H2N](#)

Transit, In+Outdoor, Artic MLT, OS2, 12f, Gel Tubes 2.8mm, Dbl Jkt - LSZH, OFNG-ST1

**Product Description**

Transit Grade, Indoor/Outdoor, Artic Multi-Loose-Tube, OS2, 12 Fibers, Gel Filled Tubes 2.8mm, Double Jacket - LSZH, OFNG-ST1

**Technical Specifications**

**Product Overview**

Product Category:	Fiber Multi-Loose Tube Cable
Suitable Applications:	Extended Distance Horizontal & Backbone Data/Telco Network, Noisy Environment, Indoor/Outdoor & Wet Locations

**Fiber Specifications**

Fiber Type:	OS2
Fiber Core Diameter:	8.2/125 µm
Fiber Diameter:	250 µm
Fiber Count:	12
Fiber Color Coding:	TIA-598-D

**Cable Construction**

Number of Active Subunits:	1
Number of Fillers:	5
Fibers Per Subunit:	12
Subunit Waterblocking:	Gel Filled
Subunit Diameter:	0.110 in (2.8 mm)
Subunit Color:	Blue
Central Strength Member:	GRP
Core Wrap:	Waterblocking tape

**Inner Jacket Specifications**

Material:	LSZH - Low Smoke Zero Halogen (Flame Retardant)
Color:	Black

**Outer Jacket Specifications**

Strength Member:	Waterblocking Aramid Yarns
Jacket Material:	LSZH - Low Smoke Zero Halogen (Flame Retardant)
Nom. Diameter:	0.606 in (15.4 mm)
Number of Ripcords:	1

**Optical Characteristics**

Wavelength	1310 nm	1550 nm
Max. Attenuation	0.35 dB/km	0.25 dB/km
Mode Field Diameter	9.2 µm	10.4 µm
1 Gigabit Ethernet Performance	5000 m	-
10 Gigabit Ethernet Performance	-	-

**Mechanical Characteristics**

Min. Bend Radius During Installation:	20x Cable OD
Min. Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	4450 N (1000 lbf)
Max. Tensile Strength During Operation:	1780 N (400 lbf)
Crush Resistance:	440 N/cm
Bulk Cable Weight:	154 lbs/kft (229 kg/km)

Temperature Range

Installation Temperature Range:	-30C to +50C
Operating Temperature Range:	-50C to +70C
Storage Temperature Range:	-50C to +70C

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Sunlight Resistance
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	OFNG-ST1, FT4
ICEA Compliance:	S-104-696

History

Update and Revision:	Revision Number: 0.26 Revision Date: 11-14-2022
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type
TT-SAG-012-H2NN	Black	Reel

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.