

Product: <u>RSWTS 4L-1025</u> 2





M12 Power Single-Ended Cordset: Male, angled, 4-pin, L-coded, shielded, blue body, 50 V AC/60 V DC, 20 A; PUR black cable, ca. 2,5mm²

Product Description

M12 Power Single-Ended Cordset: Male, angled, 4-pin, L-coded, shielded, blue body, 50 V AC/60 V DC, 20 A; PUR black cable, 2.5 mm²

Technical Drawing





Technical Specifications

Face View

Pin 1Pin 2Pin 3Pin 4brownwhiteblueblack

Technical Data

Product Family:	Power Connector
Product Sub Family:	M12 Power
Brand:	Belden
Connector Type:	Cordset, single ended
Type of Contact / Gender:	male
Connector Design:	angled
Number of Pins:	4
Coding:	L
Shielding:	Shielded
Attachment Type:	Coupling Screw
Rated Voltage:	63 V
Rated Voltage (UL):	63 V
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	50 V AC / 60 V DC
Rated Current*:	24 A
Rated Current (UL)*:	20 A

Contact Resistance:	≤ 10 mOhm	
Insulation Resistance:	> 10^9 Ohm	
Mating Cycles:	≤ 100	
Ambient Temperature (Operation)*:	40 °C to +125 °C, notice derating	
Protection Degree / IP Rating**:	IP65, IP67, IP69K	
Design Standard:	IEC 61076-2-111	
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)	
Clearance / Creepage Distance:	DIN EN 60664-1 (2008/01); VDE 0110-1	
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)	

Materials

Contact Base Material:	CuNi
Contact Plating:	Cu/Au
Contact Bearer Material:	PBT GF
Contact Bearer Color:	grey
Flammability Class (Contact Bearer):	UL 94 V-2
Molded Body Material:	TPE
Molded Body Color:	blue
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	CuZn
Attachment Plating:	Cu/Ni
O-Ring Material:	FKM

Additional Technical Data

Fastening Torque (Contact Screw):

M 12x1: (60-65) Ncm, hand-tight

Cable Data

Cable Number:	1025
Conductor Size:	2.5 mm ²
Conductor Resistance:	≤ 8.2 Ω/km (at 20 °C)
Number of Wires:	4
Minimal Bending Radius (Fixed Inst):	> 4 x D
Minimal Bending Radius (Flexible Inst):	> 7.5 x D
Cycles (Bending):	> 10 M
Conductor material:	Cu
Cable Jacket Material:	PUR
Cable Jacket Color:	black
Cable Diameter D:	ø 9.4 ±0.20 mm
Wire Insulation Material:	PP
Insulated Wire Diameter:	ø 2.55 mm
Overall Shield (Cable):	tinned copper braided screen
Ambient Temperature (Fixed Installation):	-40 °C to +90 °C (UL AWM 80°C)
Ambient Temperature (Flex Installation):	-30 °C to +90 °C (UL AWM 80°C)
Ambient Temperature (Fixed Installation short-term 100h):	-40 °C to +125 °C
Ambient Temperature (Drag Chain Inst):	-20 °C to +60 °C
UL Cable Type:	AWM: 20939
Flammability Class (Cable Jacket):	VDE 0482-332-1-2, DIN EN 60332-1-2 / IEC 60332-1 / UL VW-1, CSA FT1

Approvals

UL-File:	E497237
UL:	UL 2237; cULus
VDE:	No

Safety & Environmental Compliance

RoHS Compliant:	yes
Resistances	

Halogenfree:	DIN VDE 0472 T.815
Oil Resistance:	HD 22.10 Appendix A, DIN EN 60811-404

Notes

Note Derating:	* Notice derating
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.
Product Characteristics:	To ensure ingress protection, please check the O-ring's position before connecting. Improperly positioned O-ring leads to ingress protection potential failure.

Variants

Item #	Item Description
934852201	RSWTS 4L-1025/3 M
934852202	RSWTS 4L-1025/5 M
934852203	RSWTS 4L-1025/10 M
934852204	RSWTS 4L-1025/15 M

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulators based on their individual usage of the product.