



Product: [RTB2C2.5](#)

RailTuff™ Thin wall cable 300V 2 C 2.5 mm² TC, XLPO Ins, TCBS, XLPO Outer Jkt

Product Description

RailTuff™ Thin wall cable 300V 2 Cores 2.5 mm² Tinned Copper, XLPO Insulation, Tinned Copper Braid Shield, XLPO Outer Jacket

Technical Specifications

Product Overview

| | |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Suitable Applications: | Applicable for fixed or moderate flexing wiring inside Railway Rolling Stock like High-Speed Trains (CRH, Shinkansen, ICE, TGV), Metro, locomotives, and trolley buses, etc |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Construction Details

Conductor

| Size | Material |
|---------|--------------------|
| 2.5 mm² | TC - Tinned Copper |

Insulation

| Material | Nom. Insulation Diameter | Color Code |
|-----------------|--------------------------|------------------|
| XLP, XLPO, XLPE | 2.75 mm (0.108 in) | White#1, White#2 |

Outer Shield

| Shield Type | Material |
|-------------|--------------------|
| Braid | Tinned Copper (TC) |

Outer Jacket

| Material | Nom. Diameter |
|-----------------|--------------------|
| XLP, XLPO, XLPE | 6.80 mm (0.268 in) |

| | |
|-----------------------------------|---------------|
| Overall Cable Diameter (Nominal): | 6.8 ± 0.25 mm |
|-----------------------------------|---------------|

Mechanical Characteristics

Temperature

| Operating |
|----------------|
| -40°C to +90°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 68 mm (2.7 in) | 68 mm (2.7 in) |

| | |
|--------------------|------------------------------|
| Bulk Cable Weight: | 81.8 kg/km (55.0 lbs/1000ft) |
|--------------------|------------------------------|

Standards and Compliance

| | |
|----------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Environmental Suitability: | Indoor, Outdoor, Non-Halogenated |
| Flammability / Reaction to Fire: | IEC 60332-1-2, IEC 60332-2-25, EN 50305 |
| ISO/IEC Compliance: | IEC 61034-2 - Smoke Density Min Transmittance = 70% |
| European Halogen Free Standards: | IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3 |

Product Notes

| | |
|--------|--------------------|
| Notes: | EMEA PN: RTB2C250; |
|--------|--------------------|

History

| | |
|----------------------|-------------------------------------------------|
| Update and Revision: | Revision Number: 0.31 Revision Date: 02-15-2024 |
|----------------------|-------------------------------------------------|

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.