



**Product:** [U042A4G](#)

TC-ER XLPE/LSZH, 4+G C #2/0 Str BC, XLPE Ins M4, 1 #6 Grnd, Blk LSZH Jkt, 600V TC-ER 90C Dry/Wet SUN RES

### Product Description

UL Type TC (1277) XLPE/LSZH, 4+G Conductor 2/0 AWG (19x12) Bare Copper, XLPE Insulation M4 Color Code, 1 6AWG (7x16) Ground Wire, Black LSZH Outer Jacket, 600V TC-ER 90C Dry/Wet SUN RES

### Technical Specifications

#### Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	2/0	19x11.5	BC - Bare Copper	4
Ground	6	7x14	BC - Bare Copper	1

Conductor Count:	4
------------------	---

##### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.521 in	0.056 in
No Insulation		

##### Color Chart

Number	Color
Conductors 1 - 4	ICEA S-73-732 Table M4: Black and Numbered

##### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	1.464 in	0.103 in

#### Electrical Characteristics

##### Conductor DCR

<b>Nominal Conductor DCR</b>
.084 Ohm/1000ft

##### Current

<b>Max. Recommended Current [A]</b>
156 Amps per Conductor at 30°C

##### Voltage

UL Description	UL Voltage Rating	Voltage Rating [V]
TC	600 V RMS (Type TC)	600 V RMS (Type TC)

#### Temperature Range

UL Temp Rating:	90°C Dry, 90°C Wet
-----------------	--------------------

Operating Temperature Range:	-30°C To +90°C
Wet Temp Range:	-30°C To +90 °C

## Mechanical Characteristics

Bulk Cable Weight:	1692 lbs/1000ft
Max. Pull Tension:	4260 lbs
Min. Bend Radius/Minor Axis:	7.32 in

## Standards

NEC/(UL) Compliance:	TC-ER, XHHW-2
----------------------	---------------

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

## Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 Vertical Tray
IEEE Flammability:	1202
UL voltage rating:	600 V RMS (Type TC)

## History

Update and Revision:	Revision Number: 0.53 Revision Date: 01-10-2024
----------------------	---

© 2024 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.