

**Product:** [WireNet CAT6A Patch cord UTP](#) 

WireNet CAT6A Patch cord UTP LSZH



### Product Description

WireNet CAT6A Unshielded LSZH Patch cord, 26AWG, Stranded

### Technical Specifications

#### Product Overview

Suitable Applications:	Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

#### Physical Characteristics (Overall)

Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a sealed plastic bag.

#### Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
----------------------	----------------------------------

#### Temperature Range

Operating Temp Range:	-20°C to +60°C
-----------------------	----------------

#### Standards

Data Category:	Category 6A
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568-C.3

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

#### Related Part Numbers

Related Parts:	WireNet Jacks, WireNet Panel
----------------	------------------------------

#### Variants

Item #	Color	Length
CU-LPUABK001M	Black	1 m
CU-LPUABK002M	Black	2 m
CU-LPUABK003M	Black	3 m
CU-LPUABK004M	Black	4 m
CU-LPUABK005M	Black	5 m
CU-LPUABK007M	Black	7 m
CU-LPUABL001M	Blue	1 m
CU-LPUABL002M	Blue	2 m
CU-LPUABL003M	Blue	3 m
CU-LPUABL004M	Blue	4 m
CU-LPUABL005M	Blue	5 m

CU-LPUABL007M	Blue	7 m
CU-LPUAGY001M	Grey	1 m
CU-LPUAGY002M	Grey	2 m
CU-LPUAGY003M	Grey	3 m
CU-LPUAGY004M	Grey	4 m
CU-LPUAGY005M	Grey	5 m
CU-LPUAGY007M	Grey	7 m
CU-LPUARD001M	Red	1 m
CU-LPUARD002M	Red	2 m
CU-LPUARD003M	Red	3 m
CU-LPUARD004M	Red	4 m
CU-LPUARD005M	Red	5 m
CU-LPUARD007M	Red	7 m
CU-LPUAEW001M	White	1 m
CU-LPUAEW002M	White	2 m
CU-LPUAEW003M	White	3 m
CU-LPUAEW004M	White	4 m
CU-LPUAEW005M	White	5 m
CU-LPUAEW007M	White	7 m
CU-LPUAYL001M	Yellow	1 m
CU-LPUAYL002M	Yellow	2 m
CU-LPUAYL003M	Yellow	3 m
CU-LPUAYL004M	Yellow	4 m
CU-LPUAYL005M	Yellow	5 m
CU-LPUAYL007M	Yellow	7 m

## History

Update and Revision:	Revision Number: 0.31 Revision Date: 12-15-2021
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.