



Product: [WireNet CAT6 Patch cord STP](#)

WireNet CAT6 Patch cord STP LSZH



Product Description

WireNet CAT6 Shielded LSZH Patch cord, 26AWG, Stranded

Technical Specifications

Product Overview

Suitable Applications:	Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

Physical Characteristics (Overall)

Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a sealed plastic bag.

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
----------------------	----------------------------------

Temperature Range

Operating Temperature Range:	-20°C to +60°C
------------------------------	----------------

Standards

Data Category:	Category 6
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568-C.3

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Related Parts:	WireNet Jacks (CU-J....) , WireNet Panel (NN-UNIV-E) or KeyConnect empty panels (AX....)
----------------	--

Variants

Item #	Color	Length
CU-LPS6BK001M	Black	1 m
CU-LPS6BK002M	Black	2 m
CU-LPS6BK003M	Black	3 m
CU-LPS6BK004M	Black	4 m
CU-LPS6BK005M	Black	5 m
CU-LPS6BK007M	Black	7 m
CU-LPS6BL001M	Blue	1 m
CU-LPS6BL002M	Blue	2 m
CU-LPS6BL003M	Blue	3 m
CU-LPS6BL004M	Blue	4 m
CU-LPS6BL005M	Blue	5 m
CU-LPS6BL007M	Blue	7 m

CU-LPS6GY001M	Grey	1 m
CU-LPS6GY002M	Grey	2 m
CU-LPS6GY003M	Grey	3 m
CU-LPS6GY004M	Grey	4 m
CU-LPS6GY005M	Grey	5 m
CU-LPS6GY007M	Grey	7 m
CU-LPS6RD001M	Red	1 m
CU-LPS6RD002M	Red	2 m
CU-LPS6RD003M	Red	3 m
CU-LPS6RD004M	Red	4 m
CU-LPS6RD005M	Red	5 m
CU-LPS6RD007M	Red	7 m
CU-LPS6EW001M	White	1 m
CU-LPS6EW002M	White	2 m
CU-LPS6EW003M	White	3 m
CU-LPS6EW004M	White	4 m
CU-LPS6EW005M	White	5 m
CU-LPS6EW007M	White	7 m
CU-LPS6YL001M	Yellow	1 m
CU-LPS6YL002M	Yellow	2 m
CU-LPS6YL003M	Yellow	3 m
CU-LPS6YL004M	Yellow	4 m
CU-LPS6YL005M	Yellow	5 m
CU-LPS6YL007M	Yellow	7 m

History

Update and Revision:	Revision Number: 0.40 Revision Date: 11-21-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.