



Product: [WireNet Universal Panel](#)

WN 24-port Universal UTP/STP panel, 1U, Empty



Product Description

WireNet 24-port Universal unshielded/shielded panel, 1U, Empty

Technical Specifications

Product Overview

Suitable Applications:	Horizontal and building cabling. Support current and future Category 5e, 6 and 6A applications, such as: 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
------------------------	---

Physical Characteristics (Overall)

Height:	45 mm
Width:	483 mm
Depth:	113 mm
Front Connection:	Flush
Packaging:	Individually packaged in a box.

Connectors

Materials

Description	Material	Color
Panel	Zinc-coated Steel	Black
Body of connector	Zinc-coated Steel	Metal

Construction and Dimensions

Max Capacity:	24 connectors
---------------	---------------

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Termination Resistance:	2.5 m-Ohm

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	Keystone
Plug /Jack Compatibility:	RJ45
Termination Type:	Universal T568A/B

Standards

TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568-C.3
---------------------	-----------------------------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Related Parts:	WireNet Jacks (CU-J....) and patch cords (CU-LP....)
----------------	--

Variants

Item #	Color
NN-UNIV-E	Black

History

Update and Revision:	Revision Number: 0.30 Revision Date: 01-27-2023
----------------------	---

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.