



Product: [TF-SBB-006-RI5](#)

Factory, In+Outdoor, BO, OS2, 6f, Subunit 2.0mm, AIA, Dbl Jkt - PVC, OFCR, Ozone-UV-Oil Res

Product Description

Factory Grade, Indoor/Outdoor, Breakout, OS2, 6 Fibers, Subunits 2.0mm 900um, Aluminum Interlock Armor, Double Jacket - PVC, OFCR, Ozone-UV-Oil Resistant

Technical Specifications

Product Overview

|                        |   |
|------------------------|---|
| Product Category:      | Fiber Breakout Cable  |
| Suitable Applications: | Extended Distance Horizontal & Backbone Data/Telco Network, Noisy Environment, Indoor/Outdoor & Wet Locations, Rodent Proof |

Fiber Specifications

|                      |                          |
|----------------------|--------------------------|
| Fiber Type:          | OS2                      |
| Fiber Core Diameter: | 8.2 μm                   |
| Fiber Diameter:      | 250 μm                   |
| Buffer Material:     | PVC - Polyvinyl Chloride |
| Buffer Diameter:     | 900 μm                   |
| Fiber Count:         | 6                        |
| Fiber Color Coding:  | TIA-598-D                |

Cable Construction

|                            |                            |
|----------------------------|----------------------------|
| Number of Active Subunits: | 6                          |
| Fibers Per Subunit:        | 1                          |
| Subunit Diameter:          | 0.78 in (2.0 mm)           |
| Subunit Color:             | Yellow                     |
| Subunit Strength Members:  | Waterblocking aramid yarns |
| Central Strength Member:   | GRP                        |
| Core Wrap:                 | Waterblocking tape         |

Inner Jacket Specifications

|                  |                            |
|------------------|----------------------------|
| Strength Member: | Waterblocking Aramid Yarns |
| Material:        | PVC - Polyvinyl Chloride   |
| Nom. Diameter:   | 0.358 in (9.1 mm)          |
| Color:           | Black                      |

Armor Specifications

|                          |                                |
|--------------------------|--------------------------------|
| Armor Type and Material: | AIA - Aluminum Interlock Armor |
|--------------------------|--------------------------------|

Outer Jacket Specifications

|                  |                          |
|------------------|--------------------------|
| Jacket Material: | PVC - Polyvinyl Chloride |
| Nom. Diameter:   | 0.670 in (17.0 mm)       |

Optical Characteristics

| Wavelength       | 1310 nm    | 1550 nm    |
|------------------|------------|------------|
| Max. Attenuation | 0.40 dB/km | 0.30 dB/km |

|                                 |          |          |
|---------------------------------|----------|----------|
| Mode Field Diameter             | 9.2 μm   | 10.4 μm  |
| 1 Gigabit Ethernet Performance  | 5,000 m  | --       |
| 10 Gigabit Ethernet Performance | 10,000 m | 40,000 m |

Mechanical Characteristics

|  |                         |
|--|-------------------------|
| Min. Bend Radius During Installation:      | 20x Cable OD            |
| Min. Bend Radius During Operation:         | 10x Cable OD            |
| Max. Tensile Strength During Installation: | 1335 N (300 lbf)        |
| Max. Tensile Strength During Operation:    | 400 N (90 lbf)          |
| Crush Resistance:                          | 220 N/cm                |
| Bulk Cable Weight:                         | 195 lbs/kft (290 kg/km) |

Temperature Range

|                                 |                |
|---------------------------------|----------------|
| Installation Temperature Range: | -10°C to +60°C |
| Operating Temperature Range:    | -40°C to +70°C |
| Storage Temperature Range:      | -40°C to +70°C |

Standards and Compliance

|                                  |   |
|----------------------------------|---|
| Environmental Suitability:       | Indoor/Outdoor, Sunlight Resistance, Oil Resistance |
| Flammability / Reaction to Fire: | OFCR, FT4   |
| ICEA Compliance:                 | S-104-696   |

Product Notes

|        |                                  |
|--------|----------------------------------|
| Notes: | Ozone, Hydraulic fluid resistant |
|--------|----------------------------------|

History

|                      |   |
|----------------------|---|
| Update and Revision: | Revision Number: 0.20 Revision Date: 11-14-2022 |
|----------------------|---|

Part Numbers

Variants

| Item #          | Color | Putup Type |
|-----------------|-------|------------|
| TF-SBB-006-RI5N | Black | Reel       |

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.