


**Product:** [MRG1740](#) 



**MRG1740 - 50 Ohm Wireless Transmission Coax, RG174 Type, 26 AWG Stranded BCCS, 85% TC Braid, PVC Jkt**

## Product Description

50 Ohm Wireless Transmission Coax, RG174 Type, 26 AWG Stranded Bare Copper Covered Steel Conductor, PE Insulation, 85% Tinned Copper Braid Shield, PVC Jacket

## Technical Specifications

### Product Overview

|                        |  |
|------------------------|--|
| Suitable Applications: | Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification) |
|------------------------|--|

### Construction Details

|          |     |
|----------|-----|
| RG Type: | 174 |
|----------|-----|

#### Conductor

| No. of Elements | Size   | Stranding | Nom. Diameter | Material                         |
|-----------------|--------|-----------|---------------|----------------------------------|
| 1               | 26 AWG | Stranded  | 0.48 mm       | BCCS - Bare Copper Covered Steel |

#### Insulation

| Element             | Material          | Nom. Insulation Diameter |
|---------------------|-------------------|--------------------------|
| Insulated Conductor | PE - Polyethylene | 1.5 mm (0.059 in)        |

#### Outer Shield

| Outer Shield Type | Material           | Coverage |
|-------------------|--------------------|----------|
| Braid             | Tinned Copper (TC) | 85%      |

#### Outer Jacket

| Material                 | Nom. Diameter |
|--------------------------|---------------|
| PVC - Polyvinyl Chloride | 2.8 mm        |

|                            |                            |
|----------------------------|----------------------------|
| Outer Jacket1 Table Notes: | According to EN 50290-2-20 |
|----------------------------|----------------------------|

### Electrical Characteristics

#### Attenuation

| Frequency | Nom. Attenuation |
|-----------|------------------|
| 10 MHz    | 11 dB/100m       |
| 200 MHz   | 42 dB/100m       |
| 1000 MHz  | 110 dB/100m      |

|                          |                             |
|--------------------------|-----------------------------|
| Attenuation Table Notes: | Max. attenuation 10% higher |
|--------------------------|-----------------------------|

#### Electricals

| Max. Conductor DCR           | Nom. Capacitance Cond-to-Shield | Nom. Characteristic Impedance | Nom. Velocity of Prop. |
|------------------------------|---------------------------------|-------------------------------|------------------------|
| 317 Ohm/km (96.6 Ohm/1000ft) | 100 pF/m (30 pF/ft)             | 50 Ohm                        | 66%                    |

#### Voltage

| Voltage Rating         |
|------------------------|
| 1400 V DC / 1000 V RMS |

## Mechanical Characteristics

### Temperature

| Operating      | Installation  | Storage        |
|----------------|---------------|----------------|
| -40°C To +70°C | -5°C To +50°C | -40°C To +70°C |

Max. Pull Tension: 90 N (20 lbf)

### Standards and Compliance

|                                  |   |
|----------------------------------|---|
| Environmental Suitability:       | Indoor - Euroclass Eca                  |
| Flammability / Reaction to Fire: | IEC 60332-1-2                           |
| CPR Compliance:                  | CPR Euroclass: Eca; CPR UKCA Class: Eca |
| Military Compliance:             | MIL-C-17                                |
| European Directive Compliance:   | EU CE Mark                              |
| UK Regulation Compliance:        | UKCA Mark                               |

### History

Update and Revision: Revision Number: 0.266 Revision Date: 02-20-2026

### Part Numbers

#### Variants

| Item #        | Color | Putup Type | Length | EAN           |
|---------------|-------|------------|--------|---------------|
| MRG1740.0050  | Black | Reel       | 50 m   | 8719605102874 |
| MRG1740.00500 | Black | Reel       | 500 m  | 8719605102881 |

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.