



For more Information  
please call

1-800-Belden1



### General Description:

16 AWG pairs stranded (7x24) bare copper conductors, twisted pairs, PVC/Nylon insulation, individually shielded plus an overall Beldfoil shield (100% coverage), PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Pairs	AWG	Stranding	Conductor Material
20	16	7x24	BC - Bare Copper

Total Number of Conductors: 40

#### Insulation

##### Insulation Material:

Insulation Material
PVC/Nylon - Polyvinyl Chloride/Nylon

#### Inner Shield

##### Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

##### Inner Shield Drain Wire AWG:

AWG
18

Inner Shield Drain Wire Stranding: 7x26

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

#### Outer Shield

##### Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

##### Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
16	7x24	TC - Tinned Copper

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	2.159

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Nominal Diameter: 28.473 mm

#### Pair

##### Pair Color Code Chart:

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2
3	Black & White and Numbered 3

4	Black & White and Numbered 4
5	Black & White and Numbered 5
6	Black & White and Numbered 6
7	Black & White and Numbered 7
8	Black & White and Numbered 8
9	Black & White and Numbered 9
10	Black & White and Numbered 10
11	Black & White and Numbered 11
12	Black & White and Numbered 12
13	Black & White and Numbered 13
14	Black & White and Numbered 14
15	Black & White and Numbered 15
16	Black & White and Numbered 16
17	Black & White and Numbered 17
18	Black & White and Numbered 18
19	Black & White and Numbered 19
20	Black & White and Numbered 20

## Mechanical Characteristics (Overall)

<b>Wet Temperature Range:</b>	-30°C To +75°C
<b>Dry Temperature Range:</b>	-30°C To +90°C
<b>Bulk Cable Weight:</b>	1106.328 Kg/Km
<b>Max. Recommended Pulling Tension:</b>	8504.958 N
<b>Min. Bend Radius/Minor Axis:</b>	292.100 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

<b>NEC/(UL) Specification:</b>	NPLF, TC-ER
<b>EU Directive 2011/65/EU (ROHS II):</b>	Yes
<b>EU CE Mark:</b>	Yes
<b>EU Directive 2000/53/EC (ELV):</b>	Yes
<b>EU Directive 2002/95/EC (RoHS):</b>	Yes
<b>EU RoHS Compliance Date (mm/dd/yyyy):</b>	04/01/2005
<b>EU Directive 2002/96/EC (WEEE):</b>	Yes
<b>EU Directive 2003/11/EC (BFR):</b>	Yes
<b>CA Prop 65 (CJ for Wire &amp; Cable):</b>	Yes
<b>MII Order #39 (China RoHS):</b>	Yes
<b>Other Specification:</b>	ICEA S-73-532, S-61-402

### Flame Test

<b>UL Flame Test:</b>	UL1685 UL Loading
<b>C(UL) Flame Test:</b>	FT4
<b>IEEE Flame Test:</b>	1202

### Suitability

<b>Suitability - Burial:</b>	Yes
<b>Sunlight Resistance:</b>	Yes

### Plenum/Non-Plenum

<b>Plenum (Y/N):</b>	No
----------------------	----

## Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

METRIC MEASUREMENT VERSION

## 1044A Multi-Conductor - 600V Tray Cable

**DCR @ 20°C (Ohm/km)**

12.0413

**Nominal Outer Shield DC Resistance:**

**DCR @ 20°C (Ohm/km)**

8.82589

**Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C:** 16.635 Ohm/km

**Max. Operating Voltage - UL:**

**Voltage**

600 V RMS (NEC Type TC)

150 V RMS (NPLF)

### Notes (Overall)

**Notes:** Alternate color coding available upon request.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1044A 0102500	2,500 FT	2,062.500 LB	BLACK	C Z	TRANSFER REVIEW (20 TO 30)

**Notes:**

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 3    Revision Date: 02-13-2014

© 2020 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).