


1114A Multi-Conductor - High-Temperature Thermocouple Extension Cable

For more Information
please call

1-800-Belden1



General Description:

16 AWG pairs solid conductors, FEP insulation, overall Beldfoil shield (100% coverage), FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	16	Solid	Chromel & Constantan

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material
FEP - Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
18	7x26	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Nominal Diameter: 4.369 mm

Pair

Pair Color Code Chart:

Number	Color
1	Purple & Red

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Non-UL Temperature Rating: 200°C

Bulk Cable Weight: 47.622 Kg/Km

Max. Recommended Pulling Tension: 369.201 N

Min. Bend Radius/Minor Axis: 44.450 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: PLTC, CL3P

EU Directive 2011/65/EU (ROHS II): Yes

METRIC MEASUREMENT VERSION

1114A Multi-Conductor - High-Temperature Thermocouple Extension Cable

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
ANSI Specification:	MC 96.1-1982 Type EX

Flame Test

UL Flame Test:	UL910 Steiner Tunnel
-----------------------	----------------------

Plenum/Non-Plenum

Plenum (Y/N):	Yes
----------------------	-----

Surface Printing (Overall)

Surface Printing:	BELDEN 1114A E34972 1PR16 SHIELDED (UL) CL3P 200C PLTC SUN RES THCPL EXTN EX (2 FT., 7 DIGIT SEQUENTIAL NUMBER) FEET
--------------------------	--

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/km)
CHROMEL	541.365
CONSTANTAN	397.001

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
18.0455

Notes (Overall)

Notes: Chromel & Constantan = "Constantan is a Hoskins Manufacturing Company trademark."

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1114A 0075000	5,000 FT	160.000 LB	VIOLET	C Z	1 SH PR #16 EX FEP FEP

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 05-14-2007

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

METRIC MEASUREMENT VERSION

1114A Multi-Conductor - High-Temperature Thermocouple Extension Cable

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).