

1280P Coax - Mini Hi-Res Component Video Cable

For more Information
please call

1-800-Belden1



General Description:

25 AWG solid .018" tinned copper conductors, FPFA insulation, Duobond® foil plus a tinned copper interlocked serve shield (95% coverage), PVDF inner jackets, PVC jacket.

Usage (Overall)

Suitable Applications:

RGB Projectors, LCD Projectors, Video Distribution, Component Video, Graphic Displays, Special Effects Editing, Animation, Video Post Production, Home Theater, Offices, Boardrooms, Auditoriums, Teleconferencing, Theaters

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
6	25	Solid	TC - Tinned Copper	0.4572

Total Number of Conductors: 6

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
FPFA - Foam Perfluoroalkoxy	1.8796

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Duobond®	Tape	Aluminum Foil-Poly Tape-AluminumLightly bonded to dielectric	100
2		Interlocked Serve	TC - Tinned Copper	95

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (mm)
PVDF - Fluorocopolymer	2.8194

Inner Jacket Color Code Chart:

Number	Color
1	Red
2	Green
3	Blue
4	Yellow
5	Black
6	White

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Cabling Fillers: Cross Spine Filler

Overall Nominal Diameter: 9.373 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
UL Temperature Rating:	60°C
Non-UL Temperature Rating:	75°C
Bulk Cable Weight:	107.150 Kg/Km
Max. Recommended Pulling Tension:	444.820 N
Min. Bend Radius (Each Coax):	27.940 mm
Min. Bend Radius (Overall):	101.600 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
----------------	----------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1280R

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.285447

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

55.1208

Nominal Velocity of Propagation:

VP (%)

81

Nominal Delay:

Delay (ns/m)

4.13406

METRIC MEASUREMENT VERSION

1280P Coax - Mini Hi-Res Component Video Cable

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
111.554

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/km)
17.7174

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	1.6405
5	3.9372
50	12.4678
100	17.0612
200	23.2951
400	32.81
750	46.9183
1000	55.4489
2250	83.6655
3000	111.226

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Minimum Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
		5	850	20

Sweep Test

Sweep Testing: 5 - 850 MHz

Misc. Information (Overall)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 5 Revision Date: 09-25-2012

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.