


1340A Multi-Conductor - DataBus® for FOUNDATION Fieldbus or Profibus PA



For more Information
please call

1-800-Belden1



General Description:

18 AWG stranded (7x26) tinned copper conductors, ground wire, flame retardant polyolefin insulation, polyolefin fillers, inner and overall Beldfoil® shield (100% coverage), tinned copper drain wire, polypropylene separator, oil & sunlight resistant PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
1	8	18	7x26	TC - Tinned Copper

Total Number of Conductors: 17

Ground Wire

Ground Wire (Y/N):	Y
Ground Wire AWG:	18
Ground Wire Stranding:	7x26
Ground Wire Conductor Material:	TC - Tinned Copper
Ground Wire Insulation Material:	PVC - Polyvinyl Chloride

Insulation

Insulation Material:

Insulation Material
FRPO - Flame Retardant Polyolefin

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG	Stranding	Conductor Material
18	7x26	TC - Tinned Copper

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
20	7x28		TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 20.574 mm

1340A Multi-Conductor - DataBus® for FOUNDATION Fieldbus or Profibus PA

Pair

Pair Color Code Chart:

Number	Color
1	Blue and Orange and Numbered 1
2	Blue and Orange and Numbered 2
3	Blue and Orange and Numbered 3
4	Blue and Orange and Numbered 4
5	Blue and Orange and Numbered 5
6	Blue and Orange and Numbered 6
7	Blue and Orange and Numbered 7
8	Blue and Orange and Numbered 8
9	Green/Yellow (Ground)

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +75°C
UL Temperature Rating:	75°C
Max. Recommended Pulling Tension:	1694.764 N
Min. Bend Radius/Minor Axis:	205.740 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	TC-ER
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	11/01/2007
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Unaveraged Impedance:

Freq. (MHz)	Impedance (Ohm)
0.031	100.000

Nom. Inductance:

Inductance (µH/m)
0.722

Nom. Capacitance Cond. to Other Conductor & Shield:

METRIC MEASUREMENT VERSION

1340A Multi-Conductor - DataBus® for FOUNDATION Fieldbus or Profibus PA

Capacitance (pF/m)

147.645

Nom. Mutual Capacitance:

Capacitance (pF/m)

78.744

Maximum Capacitance Unbalance:

Capacitance (pF/m)

3.937

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

19.227

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 24.608 Ohm/km

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

0.039	0.262
-------	-------

Max. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

0.039	0.299
-------	-------

Max. Operating Voltage - UL:

Voltage

600 V RMS

Max. Recommended Current:

Description Current

Per Conductor	5.2 Amps
---------------	----------

Other Electrical Characteristic 1: Max. Propagation Delay Change From 7.812 kHz to 39.06 kHz: 518 pS/ft

Other Electrical Characteristic 2: 31.25 kBits/sec

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1340A 0035000	5,000 FT	1,730.000 LB	ORANGE	C	8 FSPR #18 FRPP+#18 PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 0 Revision Date: 07-22-2008

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).