



For more Information
please call

1-800-Belden1



General Description:

Series 11, 14 AWG solid .064" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II + aluminum braid shield (60% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	14	Solid	BCCS - Bare Copper Covered Steel	1.6256

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FPE - Foam Polyethylene	7.112

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Messenger

Messenger Diameter: 1.829 mm

Messenger Material: Galvanized Steel

Overall Cable

Overall Nominal Diameter: 10.160 x 14.732 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +80°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 116.080 Kg/Km

Max. Recommended Pulling Tension: 978.604 N

Min. Bend Radius/Minor Axis: 101.600 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Series Type:	Series 11

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

53.1522

Nominal Velocity of Propagation:

VP (%)

83

Nominal Delay:

Delay (ns/m)

3.9372

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

36.091

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

13.4521

Max. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

5	1.24678
55	3.18257
211	5.93861
270	6.72605
300	7.05415
350	7.61192
400	8.10407
450	8.69465
550	9.64614
750	11.4835
870	12.599
1000	13.8786

Max. Operating Voltage - Non-UL:

Voltage

300 V RMS

Minimum Structural Return Loss:

Description Freq. (MHz) Start Freq. (MHz) Stop Freq. (MHz) Min. SRL (dB)

		5	1000	20
--	--	---	------	----

Notes (Overall)

Notes: Sweep tested 5 MHz to 1 GHz.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1524AM 0101000	1,000 FT	88.000 LB	BLACK		#14 GIFHDLDPPE SH PVC W/MSGR

Revision Number: 2 Revision Date: 08-13-2012

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).